

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271804

Luminaire Tested: P3AS09R659827DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271804
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659827DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 249.9 lumens
Efficiency: N/A
Efficacy: 22.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271804

CATALOG NUMBER: P3AS09R659827DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1271804

CATALOG NUMBER: P3AS09R659827DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58965
5°	58243
10°	56044
15°	52486
20°	47207
25°	40091
30°	31347
35°	22352
40°	14627
45°	9055
50°	4605
55°	1606
60°	1403
65°	1401
70°	1282
75°	1271
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9055 cd/sqm

TEST NUMBER: P1271804

CATALOG NUMBER: P3AS09R659827DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.8	9.9
10°-20°	64.4	25.7
20°-30°	75.2	30.1
30°-40°	52.6	21.0
40°-50°	23.1	9.3
50°-60°	5.1	2.1
60°-70°	2.6	1.0
70°-80°	1.6	0.6
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	164.4	65.8
0°-40°	217.0	86.8
0°-60°	245.3	98.1
0°-90°	249.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	249.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	269	
5°	265	25
15°	231	64
25°	166	75
35°	84	53
45°	29	23
55°	4	5
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1271804

CATALOG NUMBER: P3AS09R659827DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	268.9
2.5°	267.9
5°	264.6
7.5°	259.1
10°	251.7
12.5°	242.5
15°	231.2
17.5°	217.5
20°	202.3
22.5°	185.1
25°	165.7
27.5°	145.3
30°	123.8
32.5°	103.2
35°	83.5
37.5°	66.3
40°	51.1
42.5°	38.6
45°	29.2
47.5°	21.4
50°	13.5
52.5°	7.0
55°	4.2
57.5°	3.7
60°	3.2
62.5°	3.0
65°	2.7
67.5°	2.2
70°	2.0
72.5°	1.7
75°	1.5
77.5°	1.2
80°	1.0
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)