

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271805

Luminaire Tested: P3AS09R659827DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271805
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659827DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 98CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 511.0 lumens
Efficiency: N/A
Efficacy: 46.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271805
CATALOG NUMBER: P3AS09R659827DE010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1271805
 CATALOG NUMBER: P3AS09R659827DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79			
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73			
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68			
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63			
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58			
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	120517
5°	119062
10°	114538
15°	107310
20°	96515
25°	81948
30°	64086
35°	45668
40°	29885
45°	18483
50°	9381
55°	3326
60°	2895
65°	2906
70°	2629
75°	2626
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18483 cd/sqm



TEST NUMBER: P1271805
 CATALOG NUMBER: P3AS09R659827DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.8	9.9
10°-20°	131.5	25.7
20°-30°	153.7	30.1
30°-40°	107.4	21.0
40°-50°	47.3	9.3
50°-60°	10.5	2.1
60°-70°	5.4	1.0
70°-80°	3.2	0.6
80°-90°	1.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	336.1	65.8
0°-40°	443.5	86.8
0°-60°	501.3	98.1
0°-90°	511.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	511.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	550	
5°	541	51
15°	473	132
25°	339	154
35°	171	107
45°	60	47
55°	9	11
65°	6	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1271805
CATALOG NUMBER: P3AS09R659827DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	549.6
2.5°	547.5
5°	540.9
7.5°	529.7
10°	514.4
12.5°	495.6
15°	472.7
17.5°	444.6
20°	413.6
22.5°	378.4
25°	338.7
27.5°	296.9
30°	253.1
32.5°	210.9
35°	170.6
37.5°	135.5
40°	104.4
42.5°	78.9
45°	59.6
47.5°	43.8
50°	27.5
52.5°	14.3
55°	8.7
57.5°	7.6
60°	6.6
62.5°	6.1
65°	5.6
67.5°	4.6
70°	4.1
72.5°	3.6
75°	3.1
77.5°	2.5
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)