

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271821

Luminaire Tested: P3AS09R659827DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271821
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659827DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 353.0 lumens
Efficiency: N/A
Efficacy: 32.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271821

CATALOG NUMBER: P3AS09R659827DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1271821

CATALOG NUMBER: P3AS09R659827DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		90
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89730
5°	87497
10°	81473
15°	73008
20°	63052
25°	52455
30°	41373
35°	30651
40°	21125
45°	13087
50°	7130
55°	4473
60°	3815
65°	3424
70°	2949
75°	2626
80°	2526
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13087 cd/sqm

TEST NUMBER: P1271821

CATALOG NUMBER: P3AS09R659827DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.9	10.5
10°-20°	89.4	25.3
20°-30°	98.8	28.0
30°-40°	71.8	20.3
40°-50°	33.6	9.5
50°-60°	11.3	3.2
60°-70°	6.5	1.9
70°-80°	3.4	1.0
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	225.2	63.8
0°-40°	297.0	84.1
0°-60°	341.9	96.9
0°-90°	353.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	353.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	409	
5°	398	37
15°	322	89
25°	217	99
35°	114	72
45°	42	34
55°	12	11
65°	7	7
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1271821

CATALOG NUMBER: P3AS09R659827DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	409.2
2.5°	406.6
5°	397.5
7.5°	383.7
10°	365.9
12.5°	345.1
15°	321.6
17.5°	296.2
20°	270.2
22.5°	243.3
25°	216.8
27.5°	189.8
30°	163.4
32.5°	137.9
35°	114.5
37.5°	93.1
40°	73.8
42.5°	56.5
45°	42.2
47.5°	30.5
50°	20.9
52.5°	14.3
55°	11.7
57.5°	10.2
60°	8.7
62.5°	7.6
65°	6.6
67.5°	5.6
70°	4.6
72.5°	4.1
75°	3.1
77.5°	2.5
80°	2.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)