

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271825

Luminaire Tested: P3AS09R709827DE010 E3CD1MB

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1271825  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R709827DE010 E3CD1MB  
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 98CRI , E3CD1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 637.0 lumens  
Efficiency: N/A  
Efficacy: 57.9 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1271825  
CATALOG NUMBER: P3AS09R709827DE010 E3CD1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P1271825  
 CATALOG NUMBER: P3AS09R709827DE010 E3CD1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78			
4	95	87	81	77	94	86	81	76	84	79	75	82	78	75	80	77	74	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			
8	76	66	59	55	75	65	59	55	64	58	55	63	58	54	62	57	54	53			
9	72	62	55	51	71	61	55	51	60	55	51	59	54	50	58	54	50	49			
10	68	58	52	47	67	57	51	47	56	51	47	56	51	47	55	50	47	46			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	126481
5°	120691
10°	114828
15°	111760
20°	107646
25°	101885
30°	94749
35°	79585
40°	51296
45°	23847
50°	6243
55°	1567
60°	1579
65°	1297
70°	1282
75°	1271
80°	1263
85°	1258

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 23847 cd/sqm



TEST NUMBER: P1271825  
 CATALOG NUMBER: P3AS09R709827DE010 E3CD1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	51.3	8.1
10°-20°	138.3	21.7
20°-30°	193.3	30.3
30°-40°	179.2	28.1
40°-50°	64.3	10.1
50°-60°	5.5	0.9
60°-70°	2.7	0.4
70°-80°	1.7	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	383.0	60.1
0°-40°	562.1	88.3
0°-60°	631.9	99.2
0°-90°	637.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	637.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	577	
5°	548	51
15°	492	138
25°	421	193
35°	297	179
45°	77	64
55°	4	5
65°	2	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1271825  
CATALOG NUMBER: P3AS09R709827DE010 E3CD1MB

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	576.8
2.5°	568.2
5°	548.3
7.5°	530.0
10°	515.7
12.5°	504.0
15°	492.3
17.5°	478.1
20°	461.3
22.5°	441.9
25°	421.1
27.5°	399.7
30°	374.2
32.5°	341.6
35°	297.3
37.5°	240.8
40°	179.2
42.5°	122.2
45°	76.9
47.5°	42.8
50°	18.3
52.5°	6.1
55°	4.1
57.5°	3.6
60°	3.6
62.5°	3.1
65°	2.5
67.5°	2.5
70°	2.0
72.5°	2.0
75°	1.5
77.5°	1.5
80°	1.0
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)