

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272687

Luminaire Tested: P3AS20R409827D010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272687
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409827D010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 98CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1998.0 lumens
Efficiency: N/A
Efficacy: 72.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.59
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272687

CATALOG NUMBER: P3AS20R409827D010 E3CB1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1272687

CATALOG NUMBER: P3AS20R409827D010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92		
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	94	92	90	89		
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	86	85		
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83	82		
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	79		
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	79	77	76		
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	73		
9	87	80	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71		
10	85	77	73	70	84	77	73	70	76	73	70	76	72	70	75	72	70	69		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1051999
5°	1046949
10°	1012829
15°	896078
20°	584644
25°	207109
30°	43931
35°	14455
40°	5296
45°	1768
50°	1467
55°	1644
60°	1228
65°	1453
70°	898
75°	1186
80°	1768
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 2352 cd/sqm

TEST NUMBER: P1272687

CATALOG NUMBER: P3AS20R409827D010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	447.5	22.4
10°-20°	1042.2	52.2
20°-30°	452.3	22.6
30°-40°	41.7	2.1
40°-50°	5.9	0.3
50°-60°	3.7	0.2
60°-70°	2.6	0.1
70°-80°	1.5	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1942.0	97.2
0°-40°	1983.7	99.3
0°-60°	1993.3	99.8
0°-90°	1998.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1998.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4798	
5°	4756	448
15°	3947	1042
25°	856	452
35°	54	42
45°	6	6
55°	4	4
65°	3	3
75°	1	1
85°	0	1
90°	0	

TEST NUMBER: P1272687

CATALOG NUMBER: P3AS20R409827D010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	4797.5
2.5°	4791.8
5°	4756.3
7.5°	4680.9
10°	4548.7
12.5°	4325.4
15°	3947.2
17.5°	3320.1
20°	2505.4
22.5°	1626.7
25°	856.0
27.5°	368.3
30°	173.5
32.5°	93.8
35°	54.0
37.5°	32.7
40°	18.5
42.5°	10.0
45°	5.7
47.5°	4.3
50°	4.3
52.5°	4.3
55°	4.3
57.5°	4.3
60°	2.8
62.5°	2.8
65°	2.8
67.5°	2.8
70°	1.4
72.5°	1.4
75°	1.4
77.5°	1.4
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)