

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272741

Luminaire Tested: P3AS20R509827D010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272741
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509827D010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 98CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1947.0 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272741

CATALOG NUMBER: P3AS20R509827D010 E3CB1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1272741

CATALOG NUMBER: P3AS20R509827D010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	66	66	65
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	678082
5°	665946
10°	639423
15°	586337
20°	517042
25°	396289
30°	215476
35°	69332
40°	16288
45°	2202
50°	1944
55°	2179
60°	1886
65°	2231
70°	1795
75°	2372
80°	1768
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 85°
Luminance: 3522 cd/sqm

TEST NUMBER: P1272741

CATALOG NUMBER: P3AS20R509827D010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	283.9	14.6
10°-20°	718.0	36.9
20°-30°	719.0	36.9
30°-40°	202.2	10.4
40°-50°	12.2	0.6
50°-60°	4.6	0.2
60°-70°	3.7	0.2
70°-80°	2.4	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1720.9	88.4
0°-40°	1923.1	98.8
0°-60°	1939.9	99.6
0°-90°	1947.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1947.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3092	
5°	3025	284
15°	2583	718
25°	1638	719
35°	259	202
45°	7	12
55°	6	5
65°	4	4
75°	3	2
85°	1	1
90°	0	

TEST NUMBER: P1272741

CATALOG NUMBER: P3AS20R509827D010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	3092.3
2.5°	3076.6
5°	3025.4
7.5°	2955.7
10°	2871.7
12.5°	2745.1
15°	2582.8
17.5°	2396.4
20°	2215.7
22.5°	1990.9
25°	1637.9
27.5°	1219.6
30°	851.0
32.5°	513.7
35°	259.0
37.5°	122.4
40°	56.9
42.5°	21.3
45°	7.1
47.5°	5.7
50°	5.7
52.5°	5.7
55°	5.7
57.5°	4.3
60°	4.3
62.5°	4.3
65°	4.3
67.5°	2.8
70°	2.8
72.5°	2.8
75°	2.8
77.5°	1.4
80°	1.4
82.5°	1.4
85°	1.4
87.5°	0.0
90°	0.0

(END OF REPORT)