

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272764

Luminaire Tested: P3AS20R509827D010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272764
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509827D010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 515.0 lumens
Efficiency: N/A
Efficacy: 18.8 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272764

CATALOG NUMBER: P3AS20R509827D010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1272764

CATALOG NUMBER: P3AS20R509827D010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	149791
5°	145762
10°	134400
15°	118207
20°	98895
25°	78416
30°	57528
35°	39565
40°	25133
45°	14048
50°	7607
55°	6384
60°	5482
65°	5085
70°	4488
75°	4151
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14048 cd/sqm

TEST NUMBER: P1272764

CATALOG NUMBER: P3AS20R509827D010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.3	11.9
10°-20°	144.2	28.0
20°-30°	147.5	28.6
30°-40°	93.5	18.2
40°-50°	37.2	7.2
50°-60°	15.1	2.9
60°-70°	9.7	1.9
70°-80°	5.0	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	353.0	68.5
0°-40°	446.6	86.7
0°-60°	498.8	96.9
0°-90°	515.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	515.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	683	
5°	662	61
15°	521	144
25°	324	147
35°	148	94
45°	45	37
55°	17	15
65°	10	10
75°	5	5
85°	1	2
90°	0	

TEST NUMBER: P1272764

CATALOG NUMBER: P3AS20R509827D010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	683.1
2.5°	678.2
5°	662.2
7.5°	637.1
10°	603.6
12.5°	563.9
15°	520.7
17.5°	473.3
20°	423.8
22.5°	374.3
25°	324.1
27.5°	273.9
30°	227.2
32.5°	185.4
35°	147.8
37.5°	115.7
40°	87.8
42.5°	64.8
45°	45.3
47.5°	30.7
50°	22.3
52.5°	18.8
55°	16.7
57.5°	14.6
60°	12.5
62.5°	11.2
65°	9.8
67.5°	8.4
70°	7.0
72.5°	5.6
75°	4.9
77.5°	3.5
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)