

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272795

Luminaire Tested: P3AS20R559827D010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272795
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559827D010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 98CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1035.0 lumens
Efficiency: N/A
Efficacy: 37.8 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272795

CATALOG NUMBER: P3AS20R559827D010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1272795

CATALOG NUMBER: P3AS20R559827D010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92		
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85		
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79		
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73		
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55		
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52		
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	281556
5°	274488
10°	255195
15°	227243
20°	193123
25°	155840
30°	118803
35°	84510
40°	55762
45°	33058
50°	19411
55°	11966
60°	10613
65°	9599
70°	8207
75°	7202
80°	7198
85°	7045

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 33058 cd/sqm

TEST NUMBER: P1272795

CATALOG NUMBER: P3AS20R559827D010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.8	11.2
10°-20°	277.5	26.8
20°-30°	293.9	28.4
30°-40°	198.6	19.2
40°-50°	87.1	8.4
50°-60°	31.2	3.0
60°-70°	18.3	1.8
70°-80°	9.6	0.9
80°-90°	3.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	687.2	66.4
0°-40°	885.9	85.6
0°-60°	1004.1	97.0
0°-90°	1035.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1035.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1284	
5°	1247	116
15°	1001	278
25°	644	294
35°	316	199
45°	107	87
55°	31	31
65°	18	18
75°	8	10
85°	3	3
90°	0	

TEST NUMBER: P1272795

CATALOG NUMBER: P3AS20R559827D010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1284.0
2.5°	1274.0
5°	1247.0
7.5°	1202.9
10°	1146.1
12.5°	1077.8
15°	1001.0
17.5°	915.7
20°	827.6
22.5°	735.1
25°	644.1
27.5°	554.5
30°	469.2
32.5°	388.2
35°	315.7
37.5°	250.3
40°	194.8
42.5°	146.5
45°	106.6
47.5°	78.2
50°	56.9
52.5°	39.8
55°	31.3
57.5°	28.4
60°	24.2
62.5°	21.3
65°	18.5
67.5°	15.6
70°	12.8
72.5°	11.4
75°	8.5
77.5°	7.1
80°	5.7
82.5°	4.3
85°	2.8
87.5°	1.4
90°	0.0

(END OF REPORT)