

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271982

Luminaire Tested: P3AS13R359827DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271982
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359827DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 268.0 lumens
Efficiency: N/A
Efficacy: 18.5 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271982
CATALOG NUMBER: P3AS13R359827DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1271982
 CATALOG NUMBER: P3AS13R359827DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	44			44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61223
5°	59916
10°	56111
15°	50375
20°	43824
25°	37333
30°	31271
35°	24922
40°	18005
45°	11412
50°	6209
55°	4320
60°	4079
65°	3788
70°	3590
75°	3050
80°	2904
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11412 cd/sqm

TEST NUMBER: P1271982
 CATALOG NUMBER: P3AS13R359827DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.3	9.5
10°-20°	61.7	23.0
20°-30°	70.8	26.4
30°-40°	57.7	21.5
40°-50°	29.1	10.9
50°-60°	10.8	4.0
60°-70°	7.3	2.7
70°-80°	4.0	1.5
80°-90°	1.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	157.8	58.9
0°-40°	215.6	80.4
0°-60°	255.5	95.3
0°-90°	268.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	268.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	279	
5°	272	25
15°	222	62
25°	154	71
35°	93	58
45°	37	29
55°	11	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1271982
CATALOG NUMBER: P3AS13R359827DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	279.2
1°	278.9
2°	278.2
3°	276.9
4°	274.9
5°	272.2
6°	268.9
7°	265.6
8°	261.3
9°	257.0
10°	252.0
11°	246.7
12°	241.1
13°	234.8
14°	228.2
15°	221.9
17.5°	205.0
20°	187.8
22.5°	170.2
25°	154.3
27.5°	138.8
30°	123.5
32.5°	108.3
35°	93.1
37.5°	77.8
40°	62.9
42.5°	49.0
45°	36.8
47.5°	26.5
50°	18.2
52.5°	13.2
55°	11.3
57.5°	10.3
60°	9.3
62.5°	8.3
65°	7.3
67.5°	6.3
70°	5.6
72.5°	4.6
75°	3.6
77.5°	3.0
80°	2.3
82.5°	1.7
85°	1.0
87.5°	0.7



TEST NUMBER: P1271982
CATALOG NUMBER: P3AS13R359827DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)