

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1271988

Luminaire Tested: P3AS13R359827DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1271988
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359827DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 215.0 lumens
Efficiency: N/A
Efficacy: 14.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1271988

CATALOG NUMBER: P3AS13R359827DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1271988

CATALOG NUMBER: P3AS13R359827DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69117
5°	67400
10°	61633
15°	52305
20°	41397
25°	31308
30°	22788
35°	15419
40°	9475
45°	5427
50°	3275
55°	2676
60°	2324
65°	2075
70°	1667
75°	1694
80°	1642
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5427 cd/sqm

TEST NUMBER: P1271988

CATALOG NUMBER: P3AS13R359827DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.3	13.2
10°-20°	63.5	29.5
20°-30°	59.4	27.6
30°-40°	36.4	16.9
40°-50°	14.3	6.7
50°-60°	6.3	2.9
60°-70°	3.9	1.8
70°-80°	2.1	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	151.2	70.3
0°-40°	187.6	87.3
0°-60°	208.2	96.9
0°-90°	215.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	215.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	315	
5°	306	28
15°	230	64
25°	129	59
35°	58	36
45°	18	14
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1271988

CATALOG NUMBER: P3AS13R359827DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	315.2
1°	315.5
2°	314.5
3°	312.5
4°	309.5
5°	306.2
6°	301.9
7°	296.9
8°	291.0
9°	284.4
10°	276.8
11°	268.8
12°	260.2
13°	250.9
14°	240.7
15°	230.4
17.5°	203.9
20°	177.4
22.5°	151.9
25°	129.4
27.5°	108.6
30°	90.0
32.5°	72.8
35°	57.6
37.5°	44.0
40°	33.1
42.5°	23.8
45°	17.5
47.5°	12.6
50°	9.6
52.5°	7.9
55°	7.0
57.5°	6.0
60°	5.3
62.5°	4.6
65°	4.0
67.5°	3.3
70°	2.6
72.5°	2.3
75°	2.0
77.5°	1.7
80°	1.3
82.5°	1.0
85°	0.7
87.5°	0.3



TEST NUMBER: P1271988

CATALOG NUMBER: P3AS13R359827DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)