

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272815

Luminaire Tested: P3AS20R609827D010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272815
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R609827D010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 98CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1496.0 lumens
Efficiency: N/A
Efficacy: 54.6 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272815

CATALOG NUMBER: P3AS20R609827D010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1272815

CATALOG NUMBER: P3AS20R609827D010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	353261
5°	349900
10°	339718
15°	318277
20°	281704
25°	235659
30°	184687
35°	133980
40°	89138
45°	55572
50°	30089
55°	8678
60°	8113
65°	7368
70°	7309
75°	7202
80°	7198
85°	7045

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 55572 cd/sqm

TEST NUMBER: P1272815

CATALOG NUMBER: P3AS20R609827D010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.7	10.0
10°-20°	389.0	26.0
20°-30°	443.3	29.6
30°-40°	314.4	21.0
40°-50°	142.7	9.5
50°-60°	30.3	2.0
60°-70°	14.6	1.0
70°-80°	9.0	0.6
80°-90°	3.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	982.0	65.6
0°-40°	1296.4	86.7
0°-60°	1469.3	98.2
0°-90°	1496.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1496.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1611	
5°	1590	150
15°	1402	389
25°	974	443
35°	500	314
45°	179	143
55°	23	30
65°	14	15
75°	8	9
85°	3	3
90°	0	

TEST NUMBER: P1272815

CATALOG NUMBER: P3AS20R609827D010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1611.0
2.5°	1605.3
5°	1589.6
7.5°	1562.6
10°	1525.7
12.5°	1473.0
15°	1402.0
17.5°	1312.4
20°	1207.2
22.5°	1093.4
25°	974.0
27.5°	851.7
30°	729.4
32.5°	612.8
35°	500.5
37.5°	401.0
40°	311.4
42.5°	236.0
45°	179.2
47.5°	133.7
50°	88.2
52.5°	41.2
55°	22.7
57.5°	19.9
60°	18.5
62.5°	17.1
65°	14.2
67.5°	12.8
70°	11.4
72.5°	10.0
75°	8.5
77.5°	7.1
80°	5.7
82.5°	4.3
85°	2.8
87.5°	1.4
90°	0.0

(END OF REPORT)