

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272014

Luminaire Tested: P3AS13R409827DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272014
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409827DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 296.1 lumens
Efficiency: N/A
Efficacy: 20.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272014

CATALOG NUMBER: P3AS13R409827DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1272014

CATALOG NUMBER: P3AS13R409827DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	66442
5°	65243
10°	61500
15°	55869
20°	49074
25°	41906
30°	34714
35°	26769
40°	19064
45°	12839
50°	6993
55°	4932
60°	4649
65°	4307
70°	3847
75°	3643
80°	2904
85°	2516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12839 cd/sqm

TEST NUMBER: P1272014

CATALOG NUMBER: P3AS13R409827DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.6	9.3
10°-20°	68.5	23.2
20°-30°	79.2	26.8
30°-40°	62.5	21.1
40°-50°	32.1	10.8
50°-60°	12.3	4.1
60°-70°	8.1	2.7
70°-80°	4.4	1.5
80°-90°	1.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	175.4	59.3
0°-40°	237.9	80.4
0°-60°	282.2	95.3
0°-90°	296.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	296.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	303	
5°	296	28
15°	246	69
25°	173	79
35°	100	62
45°	41	32
55°	13	12
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1272014

CATALOG NUMBER: P3AS13R409827DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	303.0
2.5°	301.4
5°	296.4
7.5°	287.8
10°	276.2
12.5°	262.6
15°	246.1
17.5°	228.8
20°	210.3
22.5°	191.4
25°	173.2
27.5°	155.0
30°	137.1
32.5°	118.9
35°	100.0
37.5°	82.5
40°	66.6
42.5°	53.0
45°	41.4
47.5°	30.1
50°	20.5
52.5°	14.9
55°	12.9
57.5°	11.6
60°	10.6
62.5°	9.3
65°	8.3
67.5°	7.0
70°	6.0
72.5°	5.0
75°	4.3
77.5°	3.3
80°	2.3
82.5°	2.0
85°	1.0
87.5°	0.7
90°	0.0

(END OF REPORT)