

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272823

Luminaire Tested: P3AS20R609827D010 E3DLP1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1272823  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R609827D010 E3DLP1H  
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 98CRI , E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1034.0 lumens  
Efficiency: N/A  
Efficacy: 37.7 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 27.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1272823  
CATALOG NUMBER: P3AS20R609827D010 E3DLP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1272823  
 CATALOG NUMBER: P3AS20R609827D010 E3DLP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	262040
5°	256174
10°	239831
15°	215166
20°	185026
25°	152985
30°	120879
35°	89757
40°	61830
45°	38764
50°	21321
55°	12501
60°	11227
65°	9599
70°	8207
75°	8388
80°	7198
85°	7045

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 38764 cd/sqm



TEST NUMBER: P1272823  
 CATALOG NUMBER: P3AS20R609827D010 E3DLP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.3	10.5
10°-20°	263.2	25.5
20°-30°	288.7	27.9
30°-40°	210.3	20.3
40°-50°	99.3	9.6
50°-60°	32.5	3.1
60°-70°	18.4	1.8
70°-80°	9.9	1.0
80°-90°	3.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	660.3	63.9
0°-40°	870.6	84.2
0°-60°	1002.5	97.0
0°-90°	1034.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1034.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1195	
5°	1164	108
15°	948	263
25°	632	289
35°	335	210
45°	125	99
55°	33	33
65°	18	18
75°	10	10
85°	3	3
90°	0	



TEST NUMBER: P1272823  
CATALOG NUMBER: P3AS20R609827D010 E3DLP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1195.0
2.5°	1187.9
5°	1163.8
7.5°	1126.8
10°	1077.1
12.5°	1017.4
15°	947.8
17.5°	872.5
20°	792.9
22.5°	711.9
25°	632.3
27.5°	552.8
30°	477.4
32.5°	405.0
35°	335.3
37.5°	272.8
40°	216.0
42.5°	166.3
45°	125.0
47.5°	90.9
50°	62.5
52.5°	41.2
55°	32.7
57.5°	28.4
60°	25.6
62.5°	21.3
65°	18.5
67.5°	15.6
70°	12.8
72.5°	11.4
75°	9.9
77.5°	7.1
80°	5.7
82.5°	4.3
85°	2.8
87.5°	1.4
90°	0.0

(END OF REPORT)