

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272066

Luminaire Tested: P3AS13R509827DE010 E3DL1WH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1272066  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R509827DE010 E3DL1WH  
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 98CRI , E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 499.0 lumens  
Efficiency: N/A  
Efficacy: 34.4 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1272066

CATALOG NUMBER: P3AS13R509827DE010 E3DL1WH

### Luminous Intensity Polar Plot



TEST NUMBER: P1272066

CATALOG NUMBER: P3AS13R509827DE010 E3DL1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  |  | 94  | 91  | 89  |  | 91  |
| 3   | 101 | 95  | 89  | 85  | 99  | 93  | 88  | 85  | 91  | 87  | 83  |  | 88  | 85  | 82  |  | 86  |
| 4   | 96  | 88  | 82  | 78  | 94  | 87  | 82  | 78  | 85  | 80  | 77  |  | 83  | 79  | 76  |  | 81  |
| 5   | 91  | 83  | 76  | 72  | 90  | 82  | 76  | 72  | 80  | 75  | 71  |  | 78  | 74  | 70  |  | 77  |
| 6   | 87  | 77  | 71  | 67  | 85  | 77  | 71  | 67  | 75  | 70  | 66  |  | 74  | 69  | 66  |  | 72  |
| 7   | 82  | 73  | 67  | 62  | 81  | 72  | 66  | 62  | 71  | 66  | 62  |  | 70  | 65  | 61  |  | 68  |
| 8   | 78  | 69  | 63  | 58  | 77  | 68  | 62  | 58  | 67  | 62  | 58  |  | 66  | 61  | 58  |  | 65  |
| 9   | 75  | 65  | 59  | 55  | 74  | 64  | 59  | 55  | 63  | 58  | 55  |  | 63  | 58  | 54  |  | 62  |
| 10  | 71  | 61  | 56  | 52  | 70  | 61  | 55  | 52  | 60  | 55  | 51  |  | 59  | 55  | 51  |  | 59  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 145142 |
| 5°  | 141228 |
| 10° | 130236 |
| 15° | 114530 |
| 20° | 95815  |
| 25° | 75972  |
| 30° | 55755  |
| 35° | 38334  |
| 40° | 24360  |
| 45° | 13614  |
| 50° | 7369   |
| 55° | 6193   |
| 60° | 5350   |
| 65° | 4929   |
| 70° | 4360   |
| 75° | 3982   |
| 80° | 3410   |
| 85° | 3522   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13614 cd/sqm

TEST NUMBER: P1272066

CATALOG NUMBER: P3AS13R509827DE010 E3DL1WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 59.4   | 11.9      |
| 10°-20°   | 139.7  | 28.0      |
| 20°-30°   | 142.9  | 28.6      |
| 30°-40°   | 90.6   | 18.2      |
| 40°-50°   | 36.1   | 7.2       |
| 50°-60°   | 14.6   | 2.9       |
| 60°-70°   | 9.4    | 1.9       |
| 70°-80°   | 4.8    | 1.0       |
| 80°-90°   | 1.5    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 342.1  | 68.5      |
| 0°-40°    | 432.7  | 86.7      |
| 0°-60°    | 483.4  | 96.9      |
| 0°-90°    | 499.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 499.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 662 |      |
| 5°  | 642 | 59   |
| 15° | 504 | 140  |
| 25° | 314 | 143  |
| 35° | 143 | 91   |
| 45° | 44  | 36   |
| 55° | 16  | 15   |
| 65° | 10  | 9    |
| 75° | 5   | 5    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1272066

CATALOG NUMBER: P3AS13R509827DE010 E3DL1WH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 661.9 |
| 2.5°  | 657.1 |
| 5°    | 641.6 |
| 7.5°  | 617.3 |
| 10°   | 584.9 |
| 12.5° | 546.4 |
| 15°   | 504.5 |
| 17.5° | 458.6 |
| 20°   | 410.6 |
| 22.5° | 362.7 |
| 25°   | 314.0 |
| 27.5° | 265.4 |
| 30°   | 220.2 |
| 32.5° | 179.6 |
| 35°   | 143.2 |
| 37.5° | 112.1 |
| 40°   | 85.1  |
| 42.5° | 62.8  |
| 45°   | 43.9  |
| 47.5° | 29.7  |
| 50°   | 21.6  |
| 52.5° | 18.2  |
| 55°   | 16.2  |
| 57.5° | 14.2  |
| 60°   | 12.2  |
| 62.5° | 10.8  |
| 65°   | 9.5   |
| 67.5° | 8.1   |
| 70°   | 6.8   |
| 72.5° | 5.4   |
| 75°   | 4.7   |
| 77.5° | 3.4   |
| 80°   | 2.7   |
| 82.5° | 2.0   |
| 85°   | 1.4   |
| 87.5° | 0.7   |
| 90°   | 0.0   |

(END OF REPORT)