

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272082

Luminaire Tested: P3AS13R559827DE010 E3CB1MW

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1272082  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R559827DE010 E3CB1MW  
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 98CRI , E3CB1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 899.1 lumens  
Efficiency: N/A  
Efficacy: 62.0 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1272082

CATALOG NUMBER: P3AS13R559827DE010 E3CB1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1272082

CATALOG NUMBER: P3AS13R559827DE010 E3CB1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 114 | 111 | 109 | 107 | 112 | 109 | 107 | 105 | 105 | 104 | 102 |  | 101 | 100 | 99  |  | 98  | 97  | 96  | 94  |
| 2   | 109 | 104 | 101 | 98  | 107 | 103 | 99  | 96  | 100 | 97  | 94  |  | 97  | 94  | 92  |  | 94  | 92  | 90  | 89  |
| 3   | 104 | 98  | 94  | 90  | 102 | 97  | 93  | 89  | 94  | 91  | 88  |  | 92  | 89  | 86  |  | 90  | 87  | 85  | 84  |
| 4   | 99  | 92  | 87  | 84  | 98  | 91  | 87  | 83  | 89  | 85  | 82  |  | 87  | 84  | 81  |  | 85  | 83  | 80  | 79  |
| 5   | 95  | 87  | 82  | 78  | 93  | 86  | 81  | 78  | 85  | 80  | 77  |  | 83  | 79  | 76  |  | 82  | 78  | 76  | 74  |
| 6   | 91  | 83  | 77  | 73  | 89  | 82  | 77  | 73  | 80  | 76  | 72  |  | 79  | 75  | 72  |  | 78  | 74  | 72  | 70  |
| 7   | 87  | 78  | 73  | 69  | 85  | 78  | 72  | 69  | 76  | 72  | 68  |  | 75  | 71  | 68  |  | 74  | 70  | 68  | 66  |
| 8   | 83  | 74  | 69  | 65  | 82  | 74  | 68  | 65  | 73  | 68  | 65  |  | 72  | 67  | 64  |  | 71  | 67  | 64  | 63  |
| 9   | 79  | 71  | 65  | 61  | 78  | 70  | 65  | 61  | 69  | 64  | 61  |  | 68  | 64  | 61  |  | 68  | 64  | 61  | 60  |
| 10  | 76  | 67  | 62  | 58  | 75  | 67  | 62  | 58  | 66  | 61  | 58  |  | 65  | 61  | 58  |  | 65  | 61  | 58  | 57  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 249344 |
| 5°  | 247017 |
| 10° | 256954 |
| 15° | 253373 |
| 20° | 233657 |
| 25° | 190124 |
| 30° | 115486 |
| 35° | 39966  |
| 40° | 11421  |
| 45° | 5458   |
| 50° | 2320   |
| 55° | 1032   |
| 60° | 1184   |
| 65° | 1038   |
| 70° | 898    |
| 75° | 1186   |
| 80° | 884    |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 5458 cd/sqm

TEST NUMBER: P1272082

CATALOG NUMBER: P3AS13R559827DE010 E3CB1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 108.5  | 12.1      |
| 10°-20°   | 310.2  | 34.5      |
| 20°-30°   | 345.8  | 38.5      |
| 30°-40°   | 113.1  | 12.6      |
| 40°-50°   | 14.9   | 1.7       |
| 50°-60°   | 3.2    | 0.4       |
| 60°-70°   | 1.8    | 0.2       |
| 70°-80°   | 1.2    | 0.1       |
| 80°-90°   | 0.3    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 764.5  | 85.0      |
| 0°-40°    | 877.7  | 97.6      |
| 0°-60°    | 895.8  | 99.6      |
| 0°-90°    | 899.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 899.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1137 |      |
| 5°  | 1122 | 108  |
| 15° | 1116 | 310  |
| 25° | 786  | 346  |
| 35° | 149  | 113  |
| 45° | 18   | 15   |
| 55° | 3    | 3    |
| 65° | 2    | 2    |
| 75° | 1    | 1    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1272082

CATALOG NUMBER: P3AS13R559827DE010 E3CB1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1137.1 |
| 2.5°  | 1129.0 |
| 5°    | 1122.2 |
| 7.5°  | 1138.4 |
| 10°   | 1154.0 |
| 12.5° | 1145.9 |
| 15°   | 1116.1 |
| 17.5° | 1068.9 |
| 20°   | 1001.3 |
| 22.5° | 908.1  |
| 25°   | 785.8  |
| 27.5° | 630.4  |
| 30°   | 456.1  |
| 32.5° | 279.7  |
| 35°   | 149.3  |
| 37.5° | 75.7   |
| 40°   | 39.9   |
| 42.5° | 25.7   |
| 45°   | 17.6   |
| 47.5° | 12.2   |
| 50°   | 6.8    |
| 52.5° | 4.1    |
| 55°   | 2.7    |
| 57.5° | 2.7    |
| 60°   | 2.7    |
| 62.5° | 2.0    |
| 65°   | 2.0    |
| 67.5° | 1.4    |
| 70°   | 1.4    |
| 72.5° | 1.4    |
| 75°   | 1.4    |
| 77.5° | 0.7    |
| 80°   | 0.7    |
| 82.5° | 0.7    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)