

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272891

Luminaire Tested: P3AS02R159830DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272891
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159830DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 98CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 231.0 lumens
Efficiency: N/A
Efficacy: 64.2 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272891
CATALOG NUMBER: P3AS02R159830DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1272891
 CATALOG NUMBER: P3AS02R159830DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	116	114	112	111	113	112	110	109	108	107	105	104	103	102	101	100	99	98	98	98
2	112	109	107	105	110	108	105	103	105	103	101	102	100	99	99	98	97	96	96	96
3	110	106	102	100	108	104	101	99	102	100	98	100	98	96	98	96	95	94	94	94
4	107	102	99	96	105	101	98	96	99	97	95	98	96	94	96	94	93	92	92	92
5	105	100	96	94	103	99	96	93	97	94	92	96	93	92	94	92	91	90	90	90
6	102	97	94	91	101	96	93	91	95	92	90	94	92	90	93	91	89	88	88	88
7	100	95	91	89	99	94	91	89	93	90	88	92	90	88	91	89	88	87	87	87
8	98	93	89	87	97	92	89	87	91	89	87	91	88	86	90	88	86	85	85	85
9	96	91	88	85	96	91	87	85	90	87	85	89	87	85	88	86	84	84	84	84
10	95	89	86	84	94	89	86	84	88	85	83	88	85	83	87	85	83	82	82	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	439877
5°	358705
10°	175659
15°	53757
20°	22775
25°	10307
30°	4026
35°	1847
40°	573
45°	217
50°	102
55°	38
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 217 cd/sqm



TEST NUMBER: P1272891
 CATALOG NUMBER: P3AS02R159830DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.8	54.9
10°-20°	77.8	33.7
20°-30°	20.9	9.1
30°-40°	4.6	2.0
40°-50°	0.6	0.3
50°-60°	0.1	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	225.6	97.6
0°-40°	230.2	99.6
0°-60°	231.0	100.0
0°-90°	231.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	231.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2006	
5°	1630	127
15°	237	78
25°	43	21
35°	7	5
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1272891
CATALOG NUMBER: P3AS02R159830DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2006.0
1°	1993.5
2°	1953.3
3°	1880.9
4°	1771.8
5°	1629.6
6°	1468.7
7°	1289.4
8°	1124.8
9°	950.2
10°	788.9
11°	629.3
12°	484.2
13°	372.4
14°	294.8
15°	236.8
17.5°	146.8
20°	97.6
22.5°	65.7
25°	42.6
27.5°	25.2
30°	15.9
32.5°	10.7
35°	6.9
37.5°	3.9
40°	2.0
42.5°	1.1
45°	0.7
47.5°	0.4
50°	0.3
52.5°	0.2
55°	0.1
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1272891
CATALOG NUMBER: P3AS02R159830DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)