

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272896

Luminaire Tested: P3AS02R159830DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272896
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159830DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 98CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 186.0 lumens
Efficiency: N/A
Efficacy: 51.7 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272896

CATALOG NUMBER: P3AS02R159830DE010 E3DL1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1272896

CATALOG NUMBER: P3AS02R159830DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	158891
5°	141052
10°	97950
15°	57934
20°	32996
25°	18848
30°	10432
35°	5568
40°	3092
45°	1675
50°	1023
55°	841
60°	702
65°	675
70°	577
75°	593
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1675 cd/sqm

TEST NUMBER: P1272896

CATALOG NUMBER: P3AS02R159830DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.5	29.3
10°-20°	71.9	38.7
20°-30°	37.0	19.9
30°-40°	13.9	7.5
40°-50°	4.5	2.4
50°-60°	2.0	1.1
60°-70°	1.2	0.7
70°-80°	0.7	0.4
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	163.4	87.8
0°-40°	177.3	95.3
0°-60°	183.8	98.8
0°-90°	186.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	186.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	725	
5°	641	54
15°	255	72
25°	78	37
35°	21	14
45°	5	5
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1272896

CATALOG NUMBER: P3AS02R159830DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	724.6
1°	723.2
2°	713.7
3°	695.6
4°	671.8
5°	640.8
6°	605.6
7°	567.1
8°	524.3
9°	482.0
10°	439.9
12.5°	338.5
15°	255.2
17.5°	191.0
20°	141.4
22.5°	105.5
25°	77.9
27.5°	56.8
30°	41.2
32.5°	29.2
35°	20.8
37.5°	14.9
40°	10.8
42.5°	7.7
45°	5.4
47.5°	3.9
50°	3.0
52.5°	2.5
55°	2.2
57.5°	1.8
60°	1.6
62.5°	1.4
65°	1.3
67.5°	1.1
70°	0.9
72.5°	0.9
75°	0.7
77.5°	0.5
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)