

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272116

Luminaire Tested: P3AS13R609827DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272116
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609827DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 98CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 810.0 lumens
Efficiency: N/A
Efficacy: 55.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272116
CATALOG NUMBER: P3AS13R609827DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1272116

CATALOG NUMBER: P3AS13R609827DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94	94	94	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82	82	82	82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77	77	77	77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72	72	72	72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67	67	67	67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63	63	63	63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59	59	59	59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56	56	56	56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	212242
5°	200352
10°	195142
15°	190693
20°	177302
25°	158501
30°	121057
35°	69894
40°	27137
45°	11288
50°	2490
55°	382
60°	307
65°	156
70°	192
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11288 cd/sqm



TEST NUMBER: P1272116

CATALOG NUMBER: P3AS13R609827DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.9	10.6
10°-20°	234.0	28.9
20°-30°	293.0	36.2
30°-40°	163.8	20.2
40°-50°	31.1	3.8
50°-60°	1.6	0.2
60°-70°	0.3	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	613.0	75.7
0°-40°	776.8	95.9
0°-60°	809.5	99.9
0°-90°	810.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	810.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	968	
5°	910	86
15°	840	234
25°	655	293
35°	261	164
45°	36	31
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1272116
CATALOG NUMBER: P3AS13R609827DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	967.9
1°	963.9
2°	951.3
3°	936.4
4°	922.5
5°	910.2
6°	900.9
7°	893.0
8°	887.0
9°	881.4
10°	876.4
11°	871.4
12°	865.8
13°	858.8
14°	850.6
15°	840.0
16°	827.0
17°	812.5
18°	795.9
19°	777.0
20°	759.8
21°	741.2
22°	722.0
23°	701.8
24°	679.6
25°	655.1
26°	626.2
27°	594.1
28°	558.0
29°	519.5
30°	478.1
31°	436.4
32°	393.3
32.5°	369.8
33°	348.6
34°	304.5
35°	261.1
36°	222.0
37°	180.6
37.5°	161.7
38°	143.1
39°	115.3
40°	94.8
42.5°	57.7
45°	36.4



TEST NUMBER: P1272116
CATALOG NUMBER: P3AS13R609827DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	20.2
50°	7.3
52.5°	1.7
55°	1.0
57.5°	0.7
60°	0.7
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)