

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272154

Luminaire Tested: P3AS13R659827DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272154
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659827DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 98CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 678.0 lumens
Efficiency: N/A
Efficacy: 46.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272154

CATALOG NUMBER: P3AS13R659827DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1272154

CATALOG NUMBER: P3AS13R659827DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	159899
5°	157979
10°	151968
15°	142362
20°	128041
25°	108732
30°	85051
35°	60606
40°	39646
45°	24530
50°	12452
55°	4396
60°	3859
65°	3840
70°	3462
75°	3474
80°	3410
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24530 cd/sqm

TEST NUMBER: P1272154

CATALOG NUMBER: P3AS13R659827DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.4	9.9
10°-20°	174.5	25.7
20°-30°	204.0	30.1
30°-40°	142.6	21.0
40°-50°	62.7	9.3
50°-60°	14.0	2.1
60°-70°	7.1	1.0
70°-80°	4.3	0.6
80°-90°	1.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	445.9	65.8
0°-40°	588.5	86.8
0°-60°	665.1	98.1
0°-90°	678.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	678.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	729	
5°	718	67
15°	627	175
25°	449	204
35°	226	143
45°	79	63
55°	12	14
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1272154

CATALOG NUMBER: P3AS13R659827DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	729.2
2.5°	726.5
5°	717.7
7.5°	702.8
10°	682.5
12.5°	657.5
15°	627.1
17.5°	590.0
20°	548.7
22.5°	502.1
25°	449.4
27.5°	394.0
30°	335.9
32.5°	279.8
35°	226.4
37.5°	179.8
40°	138.5
42.5°	104.7
45°	79.1
47.5°	58.1
50°	36.5
52.5°	18.9
55°	11.5
57.5°	10.1
60°	8.8
62.5°	8.1
65°	7.4
67.5°	6.1
70°	5.4
72.5°	4.7
75°	4.1
77.5°	3.4
80°	2.7
82.5°	2.0
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)