

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272160

Luminaire Tested: P3AS13R659827DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272160
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659827DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 98CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 532.0 lumens
Efficiency: N/A
Efficacy: 36.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272160

CATALOG NUMBER: P3AS13R659827DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1272160

CATALOG NUMBER: P3AS13R659827DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	94663
5°	93396
10°	90268
15°	85131
20°	78523
25°	71278
30°	63124
35°	53726
40°	42737
45°	30174
50°	17500
55°	9558
60°	8903
65°	8042
70°	7373
75°	6863
80°	5935
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30174 cd/sqm

TEST NUMBER: P1272160

CATALOG NUMBER: P3AS13R659827DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.9	7.5
10°-20°	104.9	19.7
20°-30°	134.8	25.3
30°-40°	124.7	23.4
40°-50°	75.3	14.2
50°-60°	25.7	4.8
60°-70°	15.5	2.9
70°-80°	8.7	1.6
80°-90°	2.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	279.6	52.6
0°-40°	404.4	76.0
0°-60°	505.3	95.0
0°-90°	532.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	532.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	432	
5°	424	40
15°	375	105
25°	295	135
35°	201	125
45°	97	75
55°	25	26
65°	16	15
75°	8	9
85°	2	2
90°	0	

TEST NUMBER: P1272160

CATALOG NUMBER: P3AS13R659827DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	431.7
2.5°	429.7
5°	424.3
7.5°	416.2
10°	405.4
12.5°	391.9
15°	375.0
17.5°	356.7
20°	336.5
22.5°	315.5
25°	294.6
27.5°	272.3
30°	249.3
32.5°	226.3
35°	200.7
37.5°	175.7
40°	149.3
42.5°	123.0
45°	97.3
47.5°	73.6
50°	51.3
52.5°	32.4
55°	25.0
57.5°	22.3
60°	20.3
62.5°	17.6
65°	15.5
67.5°	13.5
70°	11.5
72.5°	10.1
75°	8.1
77.5°	6.8
80°	4.7
82.5°	3.4
85°	2.0
87.5°	1.4
90°	0.0

(END OF REPORT)