

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272976

Luminaire Tested: P3AS02R309830DE010 E3CD1MMS

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1272976  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R309830DE010 E3CD1MMS  
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 98CRI , E3CD1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 228.1 lumens  
Efficiency: N/A  
Efficacy: 63.4 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1272976

CATALOG NUMBER: P3AS02R309830DE010 E3CD1MMS

### Luminous Intensity Polar Plot



TEST NUMBER: P1272976

CATALOG NUMBER: P3AS02R309830DE010 E3CD1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 99 | 98 |
| 1   | 115 | 113 | 111 | 109 | 113 | 111 | 109 | 108 | 107 | 106 | 104 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 96 | 95 |
| 2   | 111 | 108 | 105 | 102 | 109 | 106 | 104 | 101 | 103 | 101 | 99  | 100 | 99  | 97  | 98  | 96  | 95  | 94  | 93 | 92 |
| 3   | 108 | 103 | 100 | 97  | 106 | 102 | 99  | 96  | 100 | 97  | 95  | 97  | 95  | 93  | 95  | 94  | 92  | 91  | 90 | 89 |
| 4   | 105 | 100 | 96  | 93  | 103 | 98  | 95  | 92  | 97  | 94  | 91  | 95  | 92  | 90  | 93  | 91  | 89  | 88  | 87 | 86 |
| 5   | 102 | 96  | 92  | 89  | 100 | 95  | 91  | 89  | 94  | 90  | 88  | 92  | 89  | 87  | 91  | 88  | 87  | 86  | 85 | 84 |
| 6   | 99  | 93  | 89  | 86  | 98  | 92  | 88  | 86  | 91  | 88  | 85  | 90  | 87  | 85  | 89  | 86  | 84  | 83  | 82 | 81 |
| 7   | 96  | 90  | 86  | 83  | 95  | 89  | 86  | 83  | 88  | 85  | 82  | 87  | 84  | 82  | 86  | 84  | 82  | 81  | 80 | 79 |
| 8   | 94  | 87  | 83  | 81  | 93  | 87  | 83  | 80  | 86  | 83  | 80  | 85  | 82  | 80  | 84  | 82  | 79  | 78  | 77 | 76 |
| 9   | 91  | 85  | 81  | 78  | 90  | 84  | 81  | 78  | 84  | 80  | 78  | 83  | 80  | 78  | 82  | 79  | 77  | 76  | 75 | 74 |
| 10  | 89  | 83  | 79  | 76  | 88  | 82  | 78  | 76  | 82  | 78  | 76  | 81  | 78  | 76  | 80  | 77  | 75  | 74  | 73 | 72 |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 185665 |
| 5°  | 182170 |
| 10° | 161253 |
| 15° | 102157 |
| 20° | 38783  |
| 25° | 11493  |
| 30° | 4532   |
| 35° | 1392   |
| 40° | 601    |
| 45° | 217    |
| 50° | 171    |
| 55° | 153    |
| 60° | 175    |
| 65° | 208    |
| 70° | 128    |
| 75° | 169    |
| 80° | 253    |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 80°

Luminance: 253 cd/sqm

TEST NUMBER: P1272976

CATALOG NUMBER: P3AS02R309830DE010 E3CD1MMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 76.1   | 33.4      |
| 10°-20°   | 118.6  | 52.0      |
| 20°-30°   | 27.5   | 12.1      |
| 30°-40°   | 4.3    | 1.9       |
| 40°-50°   | 0.7    | 0.3       |
| 50°-60°   | 0.4    | 0.2       |
| 60°-70°   | 0.3    | 0.1       |
| 70°-80°   | 0.2    | 0.1       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 222.2  | 97.4      |
| 0°-40°    | 226.4  | 99.3      |
| 0°-60°    | 227.5  | 99.8      |
| 0°-90°    | 228.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 228.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 847 |      |
| 5°  | 828 | 76   |
| 15° | 450 | 119  |
| 25° | 48  | 28   |
| 35° | 5   | 4    |
| 45° | 1   | 1    |
| 55° | 0   | 0    |
| 65° | 0   | 0    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P1272976

CATALOG NUMBER: P3AS02R309830DE010 E3CD1MMS

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 846.7 |
| 1°    | 846.2 |
| 2°    | 843.9 |
| 3°    | 839.9 |
| 4°    | 834.9 |
| 5°    | 827.6 |
| 6°    | 818.4 |
| 7°    | 804.8 |
| 8°    | 786.2 |
| 9°    | 758.8 |
| 10°   | 724.2 |
| 11°   | 679.6 |
| 12°   | 629.3 |
| 13°   | 573.4 |
| 14°   | 512.0 |
| 15°   | 450.0 |
| 17.5° | 294.4 |
| 20°   | 166.2 |
| 22.5° | 84.9  |
| 25°   | 47.5  |
| 27.5° | 29.2  |
| 30°   | 17.9  |
| 32.5° | 9.7   |
| 35°   | 5.2   |
| 37.5° | 3.4   |
| 40°   | 2.1   |
| 42.5° | 1.3   |
| 45°   | 0.7   |
| 47.5° | 0.5   |
| 50°   | 0.5   |
| 52.5° | 0.4   |
| 55°   | 0.4   |
| 57.5° | 0.4   |
| 60°   | 0.4   |
| 62.5° | 0.4   |
| 65°   | 0.4   |
| 67.5° | 0.2   |
| 70°   | 0.2   |
| 72.5° | 0.2   |
| 75°   | 0.2   |
| 77.5° | 0.2   |
| 80°   | 0.2   |
| 82.5° | 0.0   |
| 85°   | 0.0   |
| 87.5° | 0.0   |



TEST NUMBER: P1272976  
CATALOG NUMBER: P3AS02R309830DE010 E3CD1MMS

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)