

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272209

Luminaire Tested: P3AS17R159827DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272209
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159827DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 423.0 lumens
Efficiency: N/A
Efficacy: 20.7 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272209

CATALOG NUMBER: P3AS17R159827DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1272209

CATALOG NUMBER: P3AS17R159827DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	70	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106702
5°	103808
10°	94855
15°	83088
20°	71266
25°	59520
30°	47628
35°	35710
40°	25934
45°	16963
50°	10609
55°	7187
60°	6359
65°	5863
70°	5514
75°	4999
80°	4799
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16963 cd/sqm

TEST NUMBER: P1272209

CATALOG NUMBER: P3AS17R159827DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.5	10.3
10°-20°	102.0	24.1
20°-30°	112.4	26.6
30°-40°	84.1	19.9
40°-50°	43.6	10.3
50°-60°	18.1	4.3
60°-70°	11.2	2.7
70°-80°	6.3	1.5
80°-90°	1.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	257.9	61.0
0°-40°	342.0	80.8
0°-60°	403.7	95.4
0°-90°	423.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	423.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	487	
5°	472	44
15°	366	102
25°	246	112
35°	133	84
45°	55	44
55°	19	18
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1272209

CATALOG NUMBER: P3AS17R159827DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	486.6
1°	487.1
2°	485.5
3°	482.3
4°	477.5
5°	471.6
6°	464.1
7°	456.0
8°	446.4
9°	436.2
10°	426.0
12.5°	396.5
15°	366.0
17.5°	335.5
20°	305.4
22.5°	274.9
25°	246.0
27.5°	217.0
30°	188.1
32.5°	159.7
35°	133.4
37.5°	110.9
40°	90.6
42.5°	71.8
45°	54.7
47.5°	41.3
50°	31.1
52.5°	23.0
55°	18.8
57.5°	16.6
60°	14.5
62.5°	12.9
65°	11.3
67.5°	9.6
70°	8.6
72.5°	7.0
75°	5.9
77.5°	4.8
80°	3.8
82.5°	2.7
85°	1.6
87.5°	0.5
90°	0.0

(END OF REPORT)