

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272978

Luminaire Tested: P3AS02R309830DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272978
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309830DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 98CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 226.0 lumens
Efficiency: N/A
Efficacy: 62.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272978
CATALOG NUMBER: P3AS02R309830DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1272978

CATALOG NUMBER: P3AS02R309830DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	94	94	94
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	90	90	90	90
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	88	88	88	88
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	85	85	85	85
6	99	92	88	85	97	92	88	85	90	87	84	89	86	84	88	85	83	82	82	82	82
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80	80	80	80
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	81	79	77	76	76	76	76
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	79	77	75	74	74	74	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	179810
5°	177459
10°	154951
15°	98480
20°	39017
25°	13041
30°	6077
35°	2757
40°	1059
45°	527
50°	136
55°	76
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 527 cd/sqm



TEST NUMBER: P1272978

CATALOG NUMBER: P3AS02R309830DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.7	32.6
10°-20°	114.3	50.6
20°-30°	29.5	13.0
30°-40°	6.9	3.1
40°-50°	1.4	0.6
50°-60°	0.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	217.5	96.2
0°-40°	224.4	99.3
0°-60°	226.0	100.0
0°-90°	226.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	226.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	820	
5°	806	74
15°	434	114
25°	54	29
35°	10	7
45°	2	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1272978
CATALOG NUMBER: P3AS02R309830DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	820.0
1°	819.4
2°	817.5
3°	815.3
4°	812.0
5°	806.2
6°	796.9
7°	781.2
8°	759.9
9°	732.1
10°	695.9
11°	652.8
12°	605.8
13°	551.6
14°	495.0
15°	433.8
16°	373.9
17°	316.2
18°	260.8
19°	210.0
20°	167.2
21°	131.6
22°	103.5
23°	81.9
24°	65.6
25°	53.9
26°	44.9
27°	38.2
28°	33.0
29°	28.2
30°	24.0
32.5°	15.1
35°	10.3
37.5°	6.4
40°	3.7
42.5°	2.5
45°	1.7
47.5°	1.0
50°	0.4
52.5°	0.2
55°	0.2
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1



TEST NUMBER: P1272978
CATALOG NUMBER: P3AS02R309830DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)