

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272991

Luminaire Tested: P3AS02R309830DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272991
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309830DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 98CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 146.0 lumens
Efficiency: N/A
Efficacy: 40.6 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272991

CATALOG NUMBER: P3AS02R309830DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1272991

CATALOG NUMBER: P3AS02R309830DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104		110	107	105	102		103	101	99		99	98	96		96	94	93
2	106	100	96	92		104	99	94	91		95	92	89		92	89	87		89	87	85
3	100	92	87	82		98	91	86	82		88	84	80		86	82	79		84	80	78
4	94	85	79	74		92	84	79	74		82	77	73		80	76	72		78	74	71
5	89	79	73	68		87	78	72	68		76	71	67		75	70	66		73	69	66
6	84	74	67	62		82	73	67	62		71	66	62		70	65	61		69	64	61
7	79	69	62	58		78	68	62	58		67	61	57		66	61	57		65	60	57
8	75	65	58	54		74	64	58	53		63	57	53		62	57	53		61	56	53
9	71	61	54	50		70	60	54	50		59	54	50		58	53	50		57	53	49
10	68	57	51	47		67	57	51	47		56	50	47		55	50	46		54	50	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34493
5°	33722
10°	31351
15°	27900
20°	23989
25°	20324
30°	16863
35°	13224
40°	9475
45°	6233
50°	3548
55°	2332
60°	2193
65°	2024
70°	1859
75°	1694
80°	1642
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6233 cd/sqm

TEST NUMBER: P1272991

CATALOG NUMBER: P3AS02R309830DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.2	9.7
10°-20°	34.2	23.4
20°-30°	38.5	26.4
30°-40°	30.7	21.0
40°-50°	15.8	10.8
50°-60°	5.9	4.1
60°-70°	3.9	2.7
70°-80°	2.1	1.4
80°-90°	0.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	86.9	59.5
0°-40°	117.6	80.6
0°-60°	139.4	95.5
0°-90°	146.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	146.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	157	
5°	153	14
15°	123	34
25°	84	39
35°	49	31
45°	20	16
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1272991

CATALOG NUMBER: P3AS02R309830DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	157.3
1°	157.3
2°	156.8
3°	155.9
4°	154.6
5°	153.2
6°	151.4
7°	149.1
8°	146.6
9°	143.7
10°	140.8
11°	137.6
12°	134.2
13°	130.6
14°	126.8
15°	122.9
17.5°	112.9
20°	102.8
22.5°	93.2
25°	84.0
27.5°	75.1
30°	66.6
32.5°	58.0
35°	49.4
37.5°	41.0
40°	33.1
42.5°	26.2
45°	20.1
47.5°	14.9
50°	10.4
52.5°	7.3
55°	6.1
57.5°	5.6
60°	5.0
62.5°	4.5
65°	3.9
67.5°	3.4
70°	2.9
72.5°	2.3
75°	2.0
77.5°	1.6
80°	1.3
82.5°	0.9
85°	0.5
87.5°	0.2



TEST NUMBER: P1272991

CATALOG NUMBER: P3AS02R309830DE010 E3DLD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)