

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272995

Luminaire Tested: P3AS02R309830DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272995
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309830DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 56.0 lumens
Efficiency: N/A
Efficacy: 15.6 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272995

CATALOG NUMBER: P3AS02R309830DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1272995

CATALOG NUMBER: P3AS02R309830DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	63		71	66	63		70
8	80	70	64	60	78	70	64	60	68	63	60		67	63	60		67
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	53		61	57	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	19143
5°	18534
10°	16700
15°	13825
20°	10688
25°	8033
30°	5824
35°	3882
40°	2376
45°	1395
50°	853
55°	688
60°	614
65°	519
70°	449
75°	424
80°	379
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1395 cd/sqm

TEST NUMBER: P1272995

CATALOG NUMBER: P3AS02R309830DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	7.7	13.8
10°-20°	16.8	29.9
20°-30°	15.3	27.2
30°-40°	9.2	16.5
40°-50°	3.7	6.6
50°-60°	1.6	2.9
60°-70°	1.0	1.8
70°-80°	0.5	0.9
80°-90°	0.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	39.8	71.0
0°-40°	49.0	87.4
0°-60°	54.3	97.0
0°-90°	56.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	56.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	87	
5°	84	8
15°	61	17
25°	33	15
35°	14	9
45°	4	4
55°	2	2
65°	1	1
75°	0	1
85°	0	0
90°	0	

TEST NUMBER: P1272995

CATALOG NUMBER: P3AS02R309830DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	87.3
1°	87.2
2°	86.8
3°	86.2
4°	85.4
5°	84.2
6°	82.8
7°	81.4
8°	79.5
9°	77.3
10°	75.0
11°	72.4
12°	69.6
13°	66.9
14°	63.8
15°	60.9
17.5°	53.1
20°	45.8
22.5°	39.1
25°	33.2
27.5°	27.8
30°	23.0
32.5°	18.6
35°	14.5
37.5°	11.1
40°	8.3
42.5°	6.1
45°	4.5
47.5°	3.4
50°	2.5
52.5°	2.0
55°	1.8
57.5°	1.6
60°	1.4
62.5°	1.1
65°	1.0
67.5°	0.9
70°	0.7
72.5°	0.6
75°	0.5
77.5°	0.4
80°	0.3
82.5°	0.2
85°	0.2
87.5°	0.1



TEST NUMBER: P1272995
CATALOG NUMBER: P3AS02R309830DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)