

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272246

Luminaire Tested: P3AS17R209827DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272246
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R209827DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 98CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1133.1 lumens
Efficiency: N/A
Efficacy: 55.5 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272246
CATALOG NUMBER: P3AS17R209827DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1272246
 CATALOG NUMBER: P3AS17R209827DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87	87	87	87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83	83	83	83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79	79	79	79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71	71	71	71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68	68	68	68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66	66	66	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	871706
5°	792404
10°	585649
15°	362272
20°	206891
25°	118120
30°	66238
35°	36031
40°	19751
45°	10854
50°	6345
55°	4588
60°	4342
65°	3995
70°	3526
75°	3728
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10854 cd/sqm



TEST NUMBER: P1272246
 CATALOG NUMBER: P3AS17R209827DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.7	27.5
10°-20°	445.0	39.3
20°-30°	232.3	20.5
30°-40°	89.8	7.9
40°-50°	29.2	2.6
50°-60°	11.4	1.0
60°-70°	7.6	0.7
70°-80°	4.5	0.4
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	989.0	87.3
0°-40°	1078.9	95.2
0°-60°	1119.5	98.8
0°-90°	1133.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1133.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3975	
5°	3600	312
15°	1596	445
25°	488	232
35°	135	90
45°	35	29
55°	12	11
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1272246
CATALOG NUMBER: P3AS17R209827DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3975.3
1°	3967.7
2°	3920.6
3°	3848.4
4°	3736.7
5°	3599.9
6°	3437.9
7°	3258.4
8°	3050.5
9°	2848.0
10°	2630.2
12.5°	2090.6
15°	1595.8
17.5°	1194.1
20°	886.6
22.5°	656.7
25°	488.2
27.5°	360.1
30°	261.6
32.5°	189.4
35°	134.6
37.5°	97.4
40°	69.0
42.5°	49.3
45°	35.0
47.5°	25.2
50°	18.6
52.5°	14.2
55°	12.0
57.5°	10.9
60°	9.9
62.5°	8.8
65°	7.7
67.5°	6.6
70°	5.5
72.5°	5.5
75°	4.4
77.5°	3.3
80°	2.2
82.5°	2.2
85°	1.1
87.5°	1.1
90°	0.0

(END OF REPORT)