

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273030

Luminaire Tested: P3AS02R359830DE010 E3PHLD1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1273030  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R359830DE010 E3PHLD1MW  
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 98CRI , E3PHLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 139.0 lumens  
Efficiency: N/A  
Efficacy: 38.6 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.84 / 0.92  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1273030  
CATALOG NUMBER: P3AS02R359830DE010 E3PHLD1MW

### Luminous Intensity Polar Plot



0% Up  
100% Dn

— 0°-180°    - - 45°-225°    - · - · 90°-270°



TEST NUMBER: P1273030  
 CATALOG NUMBER: P3AS02R359830DE010 E3PHLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	111	107	103	100	108	105	101	99	100	98	95	97	95	93	93	91	90	93	91	90	88
2	103	96	90	85	100	94	89	84	90	86	82	87	84	81	84	81	79	84	81	79	77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	77	73	70	68
4	88	78	71	65	86	77	70	64	75	68	64	72	67	63	70	66	62	70	66	62	60
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	65	60	56	54
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47	57	51	46	55	50	46	55	50	46	44
8	68	56	48	43	66	55	48	43	54	47	43	53	47	43	52	46	42	52	46	42	41
9	64	52	45	40	63	51	44	40	50	44	39	49	44	39	48	43	39	48	43	39	37
10	60	49	41	37	59	48	41	37	47	41	37	46	41	36	45	40	36	45	40	36	35

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	22805	22805	22805
5°	22386	22342	22386
10°	21042	21019	21042
15°	19069	19069	19092
20°	16871	16871	16871
25°	14662	14638	14638
30°	12711	12635	12685
35°	10949	10895	10949
40°	9504	9446	9504
45°	8342	8280	8280
50°	7403	7335	7335
55°	6499	6499	6499
60°	5921	5833	5921
65°	5292	5292	5292
70°	4744	4744	4744
75°	4236	4067	4236
80°	3662	3662	3662
85°	2264	2264	2264

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8342 cd/sqm



TEST NUMBER: P1273030

CATALOG NUMBER: P3AS02R359830DE010 E3PHLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	9.5	6.8
10°-20°	23.4	16.8
20°-30°	27.8	20.0
30°-40°	25.6	18.4
40°-50°	20.8	14.9
50°-60°	15.4	11.0
60°-70°	10.2	7.3
70°-80°	5.3	3.8
80°-90°	1.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	60.7	43.7
0°-40°	86.3	62.1
0°-60°	122.4	88.0
0°-90°	139.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	139.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	104	104	104	104	104	
5°	102	102	102	102	102	9
15°	84	84	84	84	84	23
25°	61	60	60	61	60	28
35°	41	41	41	41	41	26
45°	27	27	27	27	27	21
55°	17	17	17	17	17	15
65°	10	10	10	10	10	10
75°	5	5	5	5	5	5
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P1273030

CATALOG NUMBER: P3AS02R359830DE010 E3PHLD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	104.0	104.0	104.0	104.0	104.0
1°	104.0	103.9	103.9	103.9	104.0
2°	103.7	103.7	103.7	103.7	103.7
3°	103.3	103.1	103.1	103.1	103.1
4°	102.6	102.4	102.4	102.4	102.4
5°	101.7	101.5	101.5	101.5	101.7
6°	100.6	100.5	100.3	100.3	100.5
7°	99.6	99.2	99.2	99.2	99.2
8°	97.9	97.8	97.8	97.8	97.8
9°	96.3	96.0	96.2	96.2	96.2
10°	94.5	94.4	94.4	94.4	94.5
11°	92.7	92.6	92.6	92.4	92.6
12°	90.6	90.6	90.6	90.6	90.6
13°	88.6	88.4	88.4	88.4	88.6
14°	86.5	86.3	86.3	86.3	86.3
15°	84.0	84.0	84.0	84.0	84.1
17.5°	78.2	78.0	78.2	78.2	78.4
20°	72.3	72.1	72.3	72.3	72.3
22.5°	66.4	66.4	66.2	66.4	66.6
25°	60.6	60.5	60.5	60.6	60.5
27.5°	55.3	55.1	55.1	55.1	55.1
30°	50.2	49.9	49.9	50.1	50.1
32.5°	45.0	45.0	45.2	45.0	45.0
35°	40.9	40.7	40.7	40.9	40.9
37.5°	36.8	36.6	36.6	36.8	36.8
40°	33.2	33.2	33.0	33.2	33.2
42.5°	29.8	29.8	29.8	29.8	29.8
45°	26.9	26.7	26.7	26.7	26.7
47.5°	24.0	24.0	24.0	23.9	24.0
50°	21.7	21.5	21.5	21.5	21.5
52.5°	19.2	19.2	19.2	19.2	19.2
55°	17.0	17.0	17.0	17.0	17.0
57.5°	15.2	15.1	15.1	15.1	15.1
60°	13.5	13.5	13.3	13.5	13.5
62.5°	11.7	11.7	11.7	11.7	11.7
65°	10.2	10.2	10.2	10.2	10.2
67.5°	8.8	8.8	8.8	8.8	8.8
70°	7.4	7.4	7.4	7.4	7.4
72.5°	6.3	6.1	6.1	6.1	6.1
75°	5.0	5.0	4.8	5.0	5.0
77.5°	3.8	3.8	3.8	3.8	3.8
80°	2.9	2.9	2.9	2.7	2.9
82.5°	1.8	1.8	1.8	1.8	1.8
85°	0.9	0.9	0.9	0.9	0.9
87.5°	0.2	0.2	0.2	0.4	0.4



TEST NUMBER: P1273030  
CATALOG NUMBER: P3AS02R359830DE010 E3PHLD1MW

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)