

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273036

Luminaire Tested: P3AS02R409830DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273036
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-24)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409830DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 98CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 251.0 lumens
Efficiency: N/A
Efficacy: 69.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.59
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273036

CATALOG NUMBER: P3AS02R409830DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1273036

CATALOG NUMBER: P3AS02R409830DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		96
3	107	102	98	95	105	100	97	94	98	95	93		96	93	91		94
4	103	97	93	90	101	96	92	89	94	91	88		92	90	87		91
5	100	93	89	86	98	92	88	85	91	87	85		89	86	84		88
6	96	90	85	82	95	89	85	82	88	84	81		86	83	81		85
7	93	86	82	79	92	86	81	78	84	81	78		83	80	78		82
8	90	83	79	75	89	83	78	75	82	78	75		81	77	75		80
9	87	80	76	73	87	80	75	73	79	75	72		78	75	72		77
10	85	77	73	70	84	77	73	70	76	73	70		76	72	70		75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132160
5°	131521
10°	127230
15°	112577
20°	73436
25°	26010
30°	5520
35°	1820
40°	658
45°	217
50°	171
55°	191
60°	175
65°	208
70°	128
75°	169
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 336 cd/sqm

TEST NUMBER: P1273036

CATALOG NUMBER: P3AS02R409830DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.2	22.4
10°-20°	130.9	52.2
20°-30°	56.8	22.6
30°-40°	5.2	2.1
40°-50°	0.7	0.3
50°-60°	0.4	0.2
60°-70°	0.4	0.1
70°-80°	0.2	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	244.0	97.2
0°-40°	249.2	99.3
0°-60°	250.4	99.7
0°-90°	251.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	251.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	603	
5°	598	56
15°	496	131
25°	108	57
35°	7	5
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1273036

CATALOG NUMBER: P3AS02R409830DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	602.7
2.5°	602.0
5°	597.5
7.5°	588.0
10°	571.4
12.5°	543.4
15°	495.9
17.5°	417.1
20°	314.7
22.5°	204.3
25°	107.5
27.5°	46.3
30°	21.8
32.5°	11.8
35°	6.8
37.5°	4.1
40°	2.3
42.5°	1.3
45°	0.7
47.5°	0.5
50°	0.5
52.5°	0.5
55°	0.5
57.5°	0.5
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)