

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272256

Luminaire Tested: P3AS17R259827DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272256
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R259827DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R25 optic, 2700K CCT AND, 98CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1479.0 lumens
Efficiency: N/A
Efficacy: 72.5 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272256
CATALOG NUMBER: P3AS17R259827DE010 E3D1H

Luminous Intensity Polar Plot





TEST NUMBER: P1272256
 CATALOG NUMBER: P3AS17R259827DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99	100
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	97	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	96	96	96	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92	92
4	106	101	97	94	104	100	96	94	98	95	92	96	93	91	94	92	90	89	89	89	89
5	103	97	93	91	101	96	93	90	95	92	90	93	91	89	92	90	88	87	87	87	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	85	85	85
7	98	92	88	85	97	91	87	85	90	87	84	89	86	84	88	86	84	83	83	83	83
8	95	89	85	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	81	81	81
9	93	87	83	81	92	86	83	80	86	83	80	85	82	80	84	82	80	79	79	79	79
10	91	85	81	79	90	84	81	79	84	81	78	83	80	78	83	80	78	77	77	77	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1619783
5°	1500502
10°	1160945
15°	554509
20°	182833
25°	77061
30°	29878
35°	12930
40°	4294
45°	1985
50°	716
55°	421
60°	219
65°	259
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1985 cd/sqm



TEST NUMBER: P1272256
 CATALOG NUMBER: P3AS17R259827DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	599.2	40.5
10°-20°	681.5	46.1
20°-30°	158.4	10.7
30°-40°	33.2	2.2
40°-50°	5.4	0.4
50°-60°	0.9	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1439.1	97.3
0°-40°	1472.3	99.5
0°-60°	1478.6	100.0
0°-90°	1479.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1479.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7387	
5°	6817	599
15°	2443	681
25°	318	158
35°	48	33
45°	6	5
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1272256
CATALOG NUMBER: P3AS17R259827DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	7386.8
1°	7371.8
2°	7295.1
3°	7187.3
4°	7022.7
5°	6816.8
6°	6552.4
7°	6275.7
8°	5965.2
9°	5615.0
10°	5213.9
11°	4749.0
12°	4215.4
13°	3630.9
14°	3019.6
15°	2442.6
16°	1932.1
17°	1505.2
18°	1184.0
19°	947.0
20°	783.5
21°	654.8
22°	549.7
23°	459.0
24°	384.0
25°	318.5
27.5°	188.8
30°	118.0
32.5°	75.6
35°	48.3
37.5°	29.0
40°	15.0
42.5°	9.7
45°	6.4
47.5°	3.8
50°	2.1
52.5°	1.1
55°	1.1
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.0
72.5°	0.0



TEST NUMBER: P1272256
CATALOG NUMBER: P3AS17R259827DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)