

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273049

Luminaire Tested: P3AS02R409830DE010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1273049  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R409830DE010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 98CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 78.0 lumens  
Efficiency: N/A  
Efficacy: 21.7 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1273049  
CATALOG NUMBER: P3AS02R409830DE010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1273049

CATALOG NUMBER: P3AS02R409830DE010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	17499
5°	17191
10°	16210
15°	14711
20°	12928
25°	11033
30°	9141
35°	7067
40°	5009
45°	3380
50°	1842
55°	1300
60°	1228
65°	1141
70°	1026
75°	932
80°	758
85°	755

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3380 cd/sqm



TEST NUMBER: P1273049  
 CATALOG NUMBER: P3AS02R409830DE010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	7.3	9.3
10°-20°	18.1	23.2
20°-30°	20.9	26.8
30°-40°	16.4	21.1
40°-50°	8.4	10.8
50°-60°	3.2	4.1
60°-70°	2.1	2.7
70°-80°	1.2	1.5
80°-90°	0.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	46.2	59.3
0°-40°	62.7	80.4
0°-60°	74.3	95.3
0°-90°	78.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	78.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	80	
5°	78	7
15°	65	18
25°	46	21
35°	26	16
45°	11	8
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1273049

CATALOG NUMBER: P3AS02R409830DE010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	79.8
2.5°	79.4
5°	78.1
7.5°	75.8
10°	72.8
12.5°	69.2
15°	64.8
17.5°	60.3
20°	55.4
22.5°	50.4
25°	45.6
27.5°	40.8
30°	36.1
32.5°	31.3
35°	26.4
37.5°	21.7
40°	17.5
42.5°	14.0
45°	10.9
47.5°	7.9
50°	5.4
52.5°	3.9
55°	3.4
57.5°	3.1
60°	2.8
62.5°	2.4
65°	2.2
67.5°	1.8
70°	1.6
72.5°	1.3
75°	1.1
77.5°	0.9
80°	0.6
82.5°	0.5
85°	0.3
87.5°	0.2
90°	0.0

(END OF REPORT)