

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273068

Luminaire Tested: P3AS02R459830DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459830DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 98.0 lumens
Efficiency: N/A
Efficacy: 27.2 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273068

CATALOG NUMBER: P3AS02R459830DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1273068

CATALOG NUMBER: P3AS02R459830DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94		
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88		
3	104	98	93	89	102	96	92	88	94	90	87	91	88	86	89	86	84	83		
4	99	92	87	83	97	91	86	82	89	84	81	87	83	80	85	82	79	78		
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	74		
6	90	82	76	73	89	81	76	72	80	75	72	78	74	71	77	74	71	69		
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66		
8	83	74	68	65	82	73	68	64	72	68	64	71	67	64	70	67	64	62		
9	79	70	65	61	78	70	65	61	69	64	61	68	64	61	67	63	61	59		
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36795
5°	35945
10°	33043
15°	27991
20°	21725
25°	15194
30°	9571
35°	5622
40°	3177
45°	1551
50°	546
55°	421
60°	439
65°	415
70°	385
75°	339
80°	379
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1551 cd/sqm

TEST NUMBER: P1273068

CATALOG NUMBER: P3AS02R459830DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.1	15.4
10°-20°	33.9	34.5
20°-30°	28.8	29.3
30°-40°	13.7	14.0
40°-50°	4.1	4.2
50°-60°	1.1	1.1
60°-70°	0.8	0.8
70°-80°	0.5	0.5
80°-90°	0.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	77.7	79.3
0°-40°	91.4	93.3
0°-60°	96.6	98.6
0°-90°	98.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	98.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	168	
5°	163	15
15°	123	34
25°	63	29
35°	21	14
45°	5	4
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1273068

CATALOG NUMBER: P3AS02R459830DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	167.8
2.5°	166.8
5°	163.3
7.5°	157.2
10°	148.4
12.5°	136.6
15°	123.3
17.5°	108.5
20°	93.1
22.5°	77.4
25°	62.8
27.5°	49.4
30°	37.8
32.5°	28.4
35°	21.0
37.5°	15.5
40°	11.1
42.5°	7.7
45°	5.0
47.5°	2.8
50°	1.6
52.5°	1.2
55°	1.1
57.5°	1.1
60°	1.0
62.5°	0.9
65°	0.8
67.5°	0.7
70°	0.6
72.5°	0.5
75°	0.4
77.5°	0.4
80°	0.3
82.5°	0.2
85°	0.1
87.5°	0.1
90°	0.0

(END OF REPORT)