

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272313

Luminaire Tested: P3AS17R309827DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272313
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R309827DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 98CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 615.0 lumens
Efficiency: N/A
Efficacy: 30.1 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.67
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272313
CATALOG NUMBER: P3AS17R309827DE010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1272313
 CATALOG NUMBER: P3AS17R309827DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90	90	90	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	81
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68	68	68	68
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63	63	63	63
6	83	73	67	62	82	72	66	62	71	65	61	69	64	61	68	64	60	59	59	59	59
7	79	69	62	57	78	68	62	57	67	61	57	66	60	57	64	60	56	55	55	55	55
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51	51	51	51
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	199677
5°	188289
10°	160941
15°	128968
20°	100529
25°	75609
30°	55148
35°	38869
40°	26650
45°	19072
50°	15624
55°	15101
60°	15218
65°	15566
70°	16221
75°	17368
80°	17932
85°	19876

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 21168 cd/sqm



TEST NUMBER: P1272313
 CATALOG NUMBER: P3AS17R309827DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.4	12.6
10°-20°	157.9	25.7
20°-30°	143.8	23.4
30°-40°	91.6	14.9
40°-50°	49.0	8.0
50°-60°	35.9	5.8
60°-70°	30.1	4.9
70°-80°	21.1	3.4
80°-90°	8.4	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	379.1	61.6
0°-40°	470.7	76.5
0°-60°	555.5	90.3
0°-90°	615.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	615.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	911	
5°	855	77
15°	568	158
25°	312	144
35°	145	92
45°	62	49
55°	40	36
65°	30	30
75°	20	21
85°	8	8
90°	0	



TEST NUMBER: P1272313
CATALOG NUMBER: P3AS17R309827DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	910.6
2.5°	896.4
5°	855.4
7.5°	795.4
10°	722.8
12.5°	645.5
15°	568.1
17.5°	497.1
20°	430.8
22.5°	369.3
25°	312.5
27.5°	262.0
30°	217.8
32.5°	176.8
35°	145.2
37.5°	115.2
40°	93.1
42.5°	74.2
45°	61.5
47.5°	50.5
50°	45.8
52.5°	42.6
55°	39.5
57.5°	37.9
60°	34.7
62.5°	33.1
65°	30.0
67.5°	28.4
70°	25.3
72.5°	22.1
75°	20.5
77.5°	17.4
80°	14.2
82.5°	12.6
85°	7.9
87.5°	3.2
90°	0.0

(END OF REPORT)