

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273238

Luminaire Tested: P3AS05R159830DE010 E3DL1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1273238  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R159830DE010 E3DL1GPH  
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 98CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 188.0 lumens  
Efficiency: N/A  
Efficacy: 26.1 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1273238  
CATALOG NUMBER: P3AS05R159830DE010 E3DL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1273238

CATALOG NUMBER: P3AS05R159830DE010 E3DL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	74	70	68	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	160601
5°	142549
10°	98996
15°	58547
20°	33346
25°	19066
30°	10559
35°	5622
40°	3120
45°	1675
50°	1058
55°	841
60°	702
65°	675
70°	577
75°	593
80°	505
85°	503

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1675 cd/sqm



TEST NUMBER: P1273238  
 CATALOG NUMBER: P3AS05R159830DE010 E3DL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.1	29.3
10°-20°	72.7	38.7
20°-30°	37.4	19.9
30°-40°	14.0	7.5
40°-50°	4.6	2.4
50°-60°	2.0	1.0
60°-70°	1.2	0.7
70°-80°	0.7	0.4
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	165.2	87.9
0°-40°	179.2	95.3
0°-60°	185.8	98.8
0°-90°	188.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	188.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	732	
5°	648	55
15°	258	73
25°	79	37
35°	21	14
45°	5	5
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1273238  
CATALOG NUMBER: P3AS05R159830DE010 E3DL1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	732.4
1°	731.0
2°	721.4
3°	703.1
4°	679.0
5°	647.6
6°	612.1
7°	573.2
8°	529.9
9°	487.2
10°	444.6
12.5°	342.1
15°	257.9
17.5°	193.1
20°	142.9
22.5°	106.7
25°	78.8
27.5°	57.4
30°	41.7
32.5°	29.5
35°	21.0
37.5°	15.0
40°	10.9
42.5°	7.8
45°	5.4
47.5°	4.0
50°	3.1
52.5°	2.5
55°	2.2
57.5°	1.8
60°	1.6
62.5°	1.4
65°	1.3
67.5°	1.1
70°	0.9
72.5°	0.9
75°	0.7
77.5°	0.5
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)