

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272365

Luminaire Tested: P3AS17R409827DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272365
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409827DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 394.0 lumens
Efficiency: N/A
Efficacy: 19.3 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272365

CATALOG NUMBER: P3AS17R409827DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1272365

CATALOG NUMBER: P3AS17R409827DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	122688
5°	120207
10°	111911
15°	97549
20°	78617
25°	58915
30°	41424
35°	27144
40°	16431
45°	9799
50°	5868
55°	4702
60°	4254
65°	3632
70°	3462
75°	2711
80°	2652
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9799 cd/sqm

TEST NUMBER: P1272365

CATALOG NUMBER: P3AS17R409827DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.7	12.9
10°-20°	118.3	30.0
20°-30°	111.5	28.3
30°-40°	64.5	16.4
40°-50°	25.7	6.5
50°-60°	11.4	2.9
60°-70°	7.0	1.8
70°-80°	3.7	0.9
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	280.6	71.2
0°-40°	345.1	87.6
0°-60°	382.1	97.0
0°-90°	394.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	394.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	560	
5°	546	51
15°	430	118
25°	244	112
35°	101	64
45°	32	26
55°	12	11
65°	7	7
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1272365

CATALOG NUMBER: P3AS17R409827DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	559.5
2.5°	556.3
5°	546.1
7.5°	527.3
10°	502.6
12.5°	469.4
15°	429.7
17.5°	385.1
20°	336.9
22.5°	288.6
25°	243.5
27.5°	201.7
30°	163.6
32.5°	130.3
35°	101.4
37.5°	76.7
40°	57.4
42.5°	42.9
45°	31.6
47.5°	23.1
50°	17.2
52.5°	13.9
55°	12.3
57.5°	11.3
60°	9.7
62.5°	8.0
65°	7.0
67.5°	5.9
70°	5.4
72.5°	4.3
75°	3.2
77.5°	2.7
80°	2.1
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)