

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272367

Luminaire Tested: P3AS17R409827DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272367
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409827DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 98CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 804.0 lumens
Efficiency: N/A
Efficacy: 39.4 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272367

CATALOG NUMBER: P3AS17R409827DE010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1272367

CATALOG NUMBER: P3AS17R409827DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	104		104	102	100		100	99	97		97	96	95
2	107	102	98	95		105	101	97	93		97	94	91		94	92	89		92	89	88
3	102	95	90	86		100	94	89	85		91	87	84		89	85	83		86	84	81
4	97	89	83	79		95	88	83	79		86	81	78		84	80	77		82	79	76
5	92	83	77	73		90	82	77	73		81	76	72		79	75	71		77	74	71
6	87	78	72	68		86	78	72	68		76	71	67		75	70	67		73	69	66
7	83	74	68	64		82	73	68	63		72	67	63		71	66	63		70	66	62
8	79	70	64	60		78	69	64	60		68	63	59		67	63	59		66	62	59
9	76	66	60	56		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		62	57	53		61	56	53		60	56	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	250353
5°	245278
10°	228364
15°	199048
20°	160407
25°	120249
30°	84545
35°	55386
40°	33520
45°	20033
50°	11940
55°	9634
60°	8640
65°	7368
70°	6988
75°	5592
80°	5556
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20033 cd/sqm

TEST NUMBER: P1272367

CATALOG NUMBER: P3AS17R409827DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.5	12.9
10°-20°	241.5	30.0
20°-30°	227.6	28.3
30°-40°	131.6	16.4
40°-50°	52.4	6.5
50°-60°	23.2	2.9
60°-70°	14.3	1.8
70°-80°	7.5	0.9
80°-90°	2.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	572.5	71.2
0°-40°	704.1	87.6
0°-60°	779.8	97.0
0°-90°	804.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	804.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1142	
5°	1114	103
15°	877	241
25°	497	228
35°	207	132
45°	65	52
55°	25	23
65°	14	14
75°	7	8
85°	2	2
90°	0	

TEST NUMBER: P1272367

CATALOG NUMBER: P3AS17R409827DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1141.7
2.5°	1135.1
5°	1114.3
7.5°	1076.0
10°	1025.6
12.5°	957.8
15°	876.8
17.5°	785.9
20°	687.4
22.5°	588.9
25°	497.0
27.5°	411.6
30°	333.9
32.5°	266.0
35°	206.9
37.5°	156.5
40°	117.1
42.5°	87.6
45°	64.6
47.5°	47.1
50°	35.0
52.5°	28.5
55°	25.2
57.5°	23.0
60°	19.7
62.5°	16.4
65°	14.2
67.5°	12.0
70°	10.9
72.5°	8.8
75°	6.6
77.5°	5.5
80°	4.4
82.5°	3.3
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)