

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273303

Luminaire Tested: P3AS05R259830DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273303
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259830DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 98CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 297.0 lumens
Efficiency: N/A
Efficacy: 41.2 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273303
CATALOG NUMBER: P3AS05R259830DE010 E3DLD1H

Luminous Intensity Polar Plot





TEST NUMBER: P1273303
 CATALOG NUMBER: P3AS05R259830DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70586
5°	68897
10°	63838
15°	56868
20°	48864
25°	41543
30°	34182
35°	26635
40°	19179
45°	12156
50°	7198
55°	4932
60°	4561
65°	4203
70°	3783
75°	3474
80°	3283
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12156 cd/sqm



TEST NUMBER: P1273303
 CATALOG NUMBER: P3AS05R259830DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.0	9.8
10°-20°	69.5	23.4
20°-30°	78.6	26.5
30°-40°	62.2	20.9
40°-50°	31.4	10.6
50°-60°	12.6	4.2
60°-70°	8.0	2.7
70°-80°	4.4	1.5
80°-90°	1.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	177.1	59.7
0°-40°	239.3	80.6
0°-60°	283.2	95.4
0°-90°	297.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	297.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	322	
5°	313	29
15°	250	70
25°	172	79
35°	100	62
45°	39	31
55°	13	13
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1273303
CATALOG NUMBER: P3AS05R259830DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	321.9
1°	321.9
2°	320.8
3°	318.9
4°	316.3
5°	313.0
6°	308.9
7°	304.1
8°	299.0
9°	293.0
10°	286.7
11°	279.7
12°	273.1
13°	265.3
14°	257.9
15°	250.5
17.5°	229.8
20°	209.4
22.5°	190.2
25°	171.7
27.5°	153.5
30°	135.0
32.5°	117.7
35°	99.5
37.5°	82.9
40°	67.0
42.5°	52.2
45°	39.2
47.5°	29.2
50°	21.1
52.5°	15.9
55°	12.9
57.5°	11.8
60°	10.4
62.5°	9.2
65°	8.1
67.5°	7.0
70°	5.9
72.5°	5.2
75°	4.1
77.5°	3.3
80°	2.6
82.5°	1.8
85°	1.1
87.5°	0.4



TEST NUMBER: P1273303
CATALOG NUMBER: P3AS05R259830DE010 E3DLD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)