

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272402

Luminaire Tested: P3AS17R509827DE010 E3D1H

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1272402  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R509827DE010 E3D1H  
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 98CRI , E3D1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1520.0 lumens  
Efficiency: N/A  
Efficacy: 74.5 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 20.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1272402  
CATALOG NUMBER: P3AS17R509827DE010 E3D1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1272402  
 CATALOG NUMBER: P3AS17R509827DE010 E3D1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80	80	80	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76	76	76	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72	72	72	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	68	68	68	68
8	84	76	71	67	83	76	71	67	75	70	67	74	69	66	73	69	66	65	65	65	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62	62	62	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	59	59	59	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	531186
5°	517036
10°	493400
15°	446677
20°	386434
25°	316978
30°	182104
35°	56563
40°	15200
45°	5334
50°	1296
55°	421
60°	219
65°	259
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5334 cd/sqm



TEST NUMBER: P1272402  
 CATALOG NUMBER: P3AS17R509827DE010 E3D1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	220.0	14.5
10°-20°	545.2	35.9
20°-30°	573.0	37.7
30°-40°	164.0	10.8
40°-50°	16.0	1.1
50°-60°	1.3	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1338.2	88.0
0°-40°	1502.2	98.8
0°-60°	1519.6	100.0
0°-90°	1520.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1520.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2422	
5°	2349	220
15°	1968	545
25°	1310	573
35°	211	164
45°	17	16
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1272402  
CATALOG NUMBER: P3AS17R509827DE010 E3D1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2422.4
1°	2418.6
2°	2407.9
3°	2392.3
4°	2371.4
5°	2348.9
6°	2324.8
7°	2299.0
8°	2274.9
9°	2247.0
10°	2215.9
11°	2180.0
12°	2138.7
13°	2087.2
14°	2031.4
15°	1967.6
16°	1900.0
17°	1834.6
18°	1767.6
19°	1708.6
20°	1656.0
21°	1605.6
22°	1548.2
23°	1482.3
24°	1405.1
25°	1310.1
26°	1207.2
27°	1092.4
28°	978.2
29°	854.8
30°	719.2
31°	592.1
32°	475.1
32.5°	424.2
33°	372.7
34°	285.8
35°	211.3
36°	155.0
37°	115.3
37.5°	99.7
38°	86.3
39°	67.0
40°	53.1
42.5°	30.0
45°	17.2



TEST NUMBER: P1272402  
CATALOG NUMBER: P3AS17R509827DE010 E3D1H

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	9.7
50°	3.8
52.5°	1.6
55°	1.1
57.5°	1.1
60°	0.5
62.5°	0.5
65°	0.5
67.5°	0.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)