

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272413

Luminaire Tested: P3AS17R509827DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272413
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509827DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 470.0 lumens
Efficiency: N/A
Efficacy: 23.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272413

CATALOG NUMBER: P3AS17R509827DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1272413

CATALOG NUMBER: P3AS17R509827DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	95519
5°	94101
10°	89934
15°	83292
20°	74860
25°	65810
30°	55958
35°	45374
40°	34092
45°	21956
50°	10439
55°	8220
60°	7763
65°	7212
70°	6540
75°	5931
80°	5430
85°	5284

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21956 cd/sqm

TEST NUMBER: P1272413

CATALOG NUMBER: P3AS17R509827DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.1	8.5
10°-20°	102.3	21.8
20°-30°	124.3	26.4
30°-40°	105.4	22.4
40°-50°	54.7	11.6
50°-60°	19.8	4.2
60°-70°	13.7	2.9
70°-80°	7.4	1.6
80°-90°	2.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	266.7	56.7
0°-40°	372.1	79.2
0°-60°	446.6	95.0
0°-90°	470.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	470.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	436	
5°	428	40
15°	367	102
25°	272	124
35°	170	105
45°	71	55
55°	22	20
65°	14	14
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1272413

CATALOG NUMBER: P3AS17R509827DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	435.6
2.5°	434.0
5°	427.5
7.5°	417.9
10°	403.9
12.5°	386.2
15°	366.9
17.5°	344.9
20°	320.8
22.5°	296.1
25°	272.0
27.5°	246.8
30°	221.0
32.5°	195.3
35°	169.5
37.5°	144.3
40°	119.1
42.5°	94.9
45°	70.8
47.5°	47.2
50°	30.6
52.5°	23.6
55°	21.5
57.5°	19.3
60°	17.7
62.5°	15.6
65°	13.9
67.5°	11.8
70°	10.2
72.5°	8.6
75°	7.0
77.5°	5.4
80°	4.3
82.5°	3.2
85°	2.1
87.5°	1.1
90°	0.0

(END OF REPORT)