

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273362

Luminaire Tested: P3AS05R359830DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273362
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359830DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 147.0 lumens
Efficiency: N/A
Efficacy: 20.4 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273362

CATALOG NUMBER: P3AS05R359830DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1273362

CATALOG NUMBER: P3AS05R359830DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	33572
5°	32864
10°	30772
15°	27628
20°	24035
25°	20493
30°	17167
35°	13652
40°	9876
45°	6264
50°	3411
55°	2370
60°	2237
65°	2075
70°	1988
75°	1694
80°	1642
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6264 cd/sqm

TEST NUMBER: P1273362

CATALOG NUMBER: P3AS05R359830DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.9	9.5
10°-20°	33.9	23.0
20°-30°	38.8	26.4
30°-40°	31.7	21.5
40°-50°	16.0	10.9
50°-60°	5.9	4.0
60°-70°	4.0	2.7
70°-80°	2.2	1.5
80°-90°	0.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	86.6	58.9
0°-40°	118.3	80.4
0°-60°	140.2	95.3
0°-90°	147.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	147.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	153	
5°	149	14
15°	122	34
25°	85	39
35°	51	32
45°	20	16
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1273362

CATALOG NUMBER: P3AS05R359830DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	153.1
1°	153.0
2°	152.6
3°	151.9
4°	150.8
5°	149.3
6°	147.5
7°	145.7
8°	143.3
9°	141.0
10°	138.2
11°	135.3
12°	132.2
13°	128.8
14°	125.2
15°	121.7
17.5°	112.4
20°	103.0
22.5°	93.4
25°	84.7
27.5°	76.1
30°	67.8
32.5°	59.4
35°	51.0
37.5°	42.7
40°	34.5
42.5°	26.9
45°	20.2
47.5°	14.5
50°	10.0
52.5°	7.3
55°	6.2
57.5°	5.6
60°	5.1
62.5°	4.5
65°	4.0
67.5°	3.5
70°	3.1
72.5°	2.5
75°	2.0
77.5°	1.6
80°	1.3
82.5°	0.9
85°	0.5
87.5°	0.4



TEST NUMBER: P1273362

CATALOG NUMBER: P3AS05R359830DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)