

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272436

Luminaire Tested: P3AS17R559827DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272436
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559827DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 584.9 lumens
Efficiency: N/A
Efficacy: 28.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272436
CATALOG NUMBER: P3AS17R559827DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1272436
 CATALOG NUMBER: P3AS17R559827DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	95	90	86	92	88	85	89	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	160645
5°	159013
10°	153549
15°	141930
20°	122487
25°	96731
30°	68618
35°	44250
40°	26564
45°	14978
50°	8051
55°	2867
60°	2588
65°	2491
70°	2436
75°	2288
80°	2020
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14978 cd/sqm



TEST NUMBER: P1272436
 CATALOG NUMBER: P3AS17R559827DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.9	11.6
10°-20°	172.9	29.6
20°-30°	181.2	31.0
30°-40°	105.7	18.1
40°-50°	39.5	6.8
50°-60°	9.3	1.6
60°-70°	4.8	0.8
70°-80°	2.8	0.5
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	422.0	72.1
0°-40°	527.7	90.2
0°-60°	576.5	98.6
0°-90°	584.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	584.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	733	
5°	722	68
15°	625	173
25°	400	181
35°	165	106
45°	48	40
55°	8	9
65°	5	5
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P1272436
CATALOG NUMBER: P3AS17R559827DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	732.6
2.5°	730.4
5°	722.4
7.5°	709.5
10°	689.6
12.5°	661.7
15°	625.2
17.5°	579.1
20°	524.9
22.5°	464.2
25°	399.8
27.5°	333.8
30°	271.0
32.5°	214.1
35°	165.3
37.5°	125.6
40°	92.8
42.5°	66.5
45°	48.3
47.5°	34.9
50°	23.6
52.5°	13.4
55°	7.5
57.5°	6.4
60°	5.9
62.5°	5.4
65°	4.8
67.5°	4.3
70°	3.8
72.5°	3.2
75°	2.7
77.5°	2.1
80°	1.6
82.5°	1.1
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)