

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273387

Luminaire Tested: P3AS05R409830DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273387
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409830DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 98CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 518.0 lumens
Efficiency: N/A
Efficacy: 71.9 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273387
CATALOG NUMBER: P3AS05R409830DE010 E3D1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1273387

CATALOG NUMBER: P3AS05R409830DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96	96	96	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92	92	92	92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88	88	88	88
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	85	85	85	85
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	82	82	82	82
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	79	79	79	79
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77	76	76	76	76
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	73	73	73	73
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	70	70	70	70
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	74	71	69	68	68	68	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	264036
5°	262139
10°	255261
15°	228015
20°	151190
25°	56640
30°	15142
35°	5916
40°	2118
45°	1023
50°	307
55°	153
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1023 cd/sqm



TEST NUMBER: P1273387
 CATALOG NUMBER: P3AS05R409830DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.4	21.7
10°-20°	266.1	51.4
20°-30°	120.7	23.3
30°-40°	15.6	3.0
40°-50°	2.7	0.5
50°-60°	0.3	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	499.2	96.4
0°-40°	514.9	99.4
0°-60°	517.9	100.0
0°-90°	518.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	518.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1204	
5°	1191	112
15°	1004	266
25°	234	121
35°	22	16
45°	3	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1273387

CATALOG NUMBER: P3AS05R409830DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1204.1
1°	1203.4
2°	1201.6
3°	1198.8
4°	1195.4
5°	1190.9
6°	1185.6
7°	1179.1
8°	1171.1
9°	1160.2
10°	1146.4
11°	1130.3
12°	1108.7
13°	1082.1
14°	1047.2
15°	1004.4
16°	949.9
17°	887.7
18°	813.0
19°	734.1
20°	647.9
21°	561.8
22°	476.9
23°	392.4
24°	309.4
25°	234.1
26°	173.4
27°	126.9
28°	95.4
29°	74.2
30°	59.8
31°	49.5
32°	41.3
32.5°	37.7
33°	34.1
34°	27.7
35°	22.1
36°	17.4
37°	13.8
37.5°	12.3
38°	10.9
39°	9.1
40°	7.4
42.5°	4.9
45°	3.3



TEST NUMBER: P1273387
CATALOG NUMBER: P3AS05R409830DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	2.0
50°	0.9
52.5°	0.4
55°	0.4
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)