

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273399

Luminaire Tested: P3AS05R409830DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273399
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409830DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 98CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 331.0 lumens
Efficiency: N/A
Efficacy: 46.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273399

CATALOG NUMBER: P3AS05R409830DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1273399

CATALOG NUMBER: P3AS05R409830DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74292
5°	72947
10°	68781
15°	62475
20°	54885
25°	46866
30°	38816
35°	29928
40°	21297
45°	14358
50°	7846
55°	5505
60°	5219
65°	4825
70°	4296
75°	4067
80°	3283
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14358 cd/sqm

TEST NUMBER: P1273399

CATALOG NUMBER: P3AS05R409830DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	30.9	9.3
10°-20°	76.7	23.2
20°-30°	88.6	26.8
30°-40°	69.8	21.1
40°-50°	35.9	10.8
50°-60°	13.7	4.1
60°-70°	9.1	2.7
70°-80°	4.9	1.5
80°-90°	1.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	196.2	59.3
0°-40°	266.0	80.3
0°-60°	315.6	95.3
0°-90°	331.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	331.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	339	
5°	331	31
15°	275	77
25°	194	89
35°	112	70
45°	46	36
55°	14	14
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1273399

CATALOG NUMBER: P3AS05R409830DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	338.8
2.5°	337.0
5°	331.4
7.5°	321.8
10°	308.9
12.5°	293.7
15°	275.2
17.5°	255.9
20°	235.2
22.5°	214.0
25°	193.7
27.5°	173.3
30°	153.3
32.5°	132.9
35°	111.8
37.5°	92.2
40°	74.4
42.5°	59.3
45°	46.3
47.5°	33.7
50°	23.0
52.5°	16.7
55°	14.4
57.5°	13.0
60°	11.9
62.5°	10.4
65°	9.3
67.5°	7.8
70°	6.7
72.5°	5.6
75°	4.8
77.5°	3.7
80°	2.6
82.5°	2.2
85°	1.1
87.5°	0.7
90°	0.0

(END OF REPORT)