

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273411

Luminaire Tested: P3AS05R459830DE010 E3CD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273411
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459830DE010 E3CD1MW
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 98CRI , E3CD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 496.0 lumens
Efficiency: N/A
Efficacy: 68.9 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273411

CATALOG NUMBER: P3AS05R459830DE010 E3CD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1273411

CATALOG NUMBER: P3AS05R459830DE010 E3CD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87		
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	83		
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79		
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75		
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	72		
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69		
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66		
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	215049
5°	216200
10°	209549
15°	175597
20°	134225
25°	81706
30°	34005
35°	10895
40°	3378
45°	682
50°	512
55°	573
60°	482
65°	571
70°	449
75°	593
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 682 cd/sqm

TEST NUMBER: P1273411

CATALOG NUMBER: P3AS05R459830DE010 E3CD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.6	18.7
10°-20°	212.6	42.9
20°-30°	153.1	30.9
30°-40°	31.8	6.4
40°-50°	2.9	0.6
50°-60°	1.2	0.2
60°-70°	0.9	0.2
70°-80°	0.6	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	458.3	92.4
0°-40°	490.1	98.8
0°-60°	494.2	99.7
0°-90°	496.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	496.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	981	
5°	982	93
15°	774	213
25°	338	153
35°	41	32
45°	2	3
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1273411

CATALOG NUMBER: P3AS05R459830DE010 E3CD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	980.7
2.5°	981.0
5°	982.2
7.5°	975.1
10°	941.1
12.5°	870.1
15°	773.5
17.5°	674.7
20°	575.2
22.5°	460.9
25°	337.7
27.5°	222.7
30°	134.3
32.5°	75.1
35°	40.7
37.5°	22.9
40°	11.8
42.5°	5.2
45°	2.2
47.5°	1.5
50°	1.5
52.5°	1.5
55°	1.5
57.5°	1.1
60°	1.1
62.5°	1.1
65°	1.1
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)