

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272465

Luminaire Tested: P3AS17R609827DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272465
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609827DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 564.0 lumens
Efficiency: N/A
Efficacy: 27.6 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272465
CATALOG NUMBER: P3AS17R609827DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1272465

CATALOG NUMBER: P3AS17R609827DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85				85
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79				79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73				73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68				68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63				63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59				59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55				55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51				51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48				48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133169
5°	131917
10°	128076
15°	119978
20°	106199
25°	88844
30°	69631
35°	50514
40°	33606
45°	20932
50°	11326
55°	3288
60°	3070
65°	2802
70°	2757
75°	2711
80°	2652
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20932 cd/sqm



TEST NUMBER: P1272465
 CATALOG NUMBER: P3AS17R609827DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.4	10.0
10°-20°	146.6	26.0
20°-30°	167.1	29.6
30°-40°	118.5	21.0
40°-50°	53.8	9.5
50°-60°	11.4	2.0
60°-70°	5.5	1.0
70°-80°	3.4	0.6
80°-90°	1.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	370.2	65.6
0°-40°	488.7	86.7
0°-60°	553.9	98.2
0°-90°	564.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	564.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	607	
5°	599	56
15°	528	147
25°	367	167
35°	189	119
45°	68	54
55°	9	11
65°	5	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1272465
CATALOG NUMBER: P3AS17R609827DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	607.3
2.5°	605.2
5°	599.3
7.5°	589.1
10°	575.2
12.5°	555.3
15°	528.5
17.5°	494.8
20°	455.1
22.5°	412.2
25°	367.2
27.5°	321.1
30°	275.0
32.5°	231.0
35°	188.7
37.5°	151.2
40°	117.4
42.5°	89.0
45°	67.5
47.5°	50.4
50°	33.2
52.5°	15.5
55°	8.6
57.5°	7.5
60°	7.0
62.5°	6.4
65°	5.4
67.5°	4.8
70°	4.3
72.5°	3.8
75°	3.2
77.5°	2.7
80°	2.1
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)