

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272500

Luminaire Tested: P3AS17R659827DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272500
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659827DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 423.0 lumens
Efficiency: N/A
Efficacy: 20.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272500

CATALOG NUMBER: P3AS17R659827DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1272500

CATALOG NUMBER: P3AS17R659827DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75279
5°	74268
10°	71764
15°	67696
20°	62422
25°	56665
30°	50185
35°	42724
40°	33978
45°	24002
50°	13919
55°	7608
60°	7061
65°	6434
70°	5834
75°	5422
80°	4799
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24002 cd/sqm

TEST NUMBER: P1272500

CATALOG NUMBER: P3AS17R659827DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.7	7.5
10°-20°	83.4	19.7
20°-30°	107.2	25.3
30°-40°	99.2	23.4
40°-50°	59.9	14.2
50°-60°	20.4	4.8
60°-70°	12.3	2.9
70°-80°	6.9	1.6
80°-90°	2.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	222.3	52.6
0°-40°	321.5	76.0
0°-60°	401.8	95.0
0°-90°	423.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	423.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	343	
5°	337	32
15°	298	83
25°	234	107
35°	160	99
45°	77	60
55°	20	20
65°	12	12
75°	6	7
85°	2	2
90°	0	

TEST NUMBER: P1272500

CATALOG NUMBER: P3AS17R659827DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	343.3
2.5°	341.7
5°	337.4
7.5°	330.9
10°	322.3
12.5°	311.6
15°	298.2
17.5°	283.6
20°	267.5
22.5°	250.9
25°	234.2
27.5°	216.5
30°	198.2
32.5°	180.0
35°	159.6
37.5°	139.7
40°	118.7
42.5°	97.8
45°	77.4
47.5°	58.6
50°	40.8
52.5°	25.8
55°	19.9
57.5°	17.7
60°	16.1
62.5°	14.0
65°	12.4
67.5°	10.7
70°	9.1
72.5°	8.1
75°	6.4
77.5°	5.4
80°	3.8
82.5°	2.7
85°	1.6
87.5°	1.1
90°	0.0

(END OF REPORT)