

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273493

Luminaire Tested: P3AS05R609830DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273493
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609830DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 98CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 479.0 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273493

CATALOG NUMBER: P3AS05R609830DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1273493

CATALOG NUMBER: P3AS05R609830DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	114377
5°	109839
10°	113091
15°	114552
20°	101159
25°	85239
30°	69125
35°	45026
40°	20667
45°	7939
50°	2661
55°	726
60°	658
65°	571
70°	449
75°	593
80°	505
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7939 cd/sqm

TEST NUMBER: P1273493

CATALOG NUMBER: P3AS05R609830DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.0	10.0
10°-20°	138.2	28.8
20°-30°	161.2	33.6
30°-40°	104.0	21.7
40°-50°	23.3	4.9
50°-60°	2.3	0.5
60°-70°	1.1	0.2
70°-80°	0.6	0.1
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	347.4	72.5
0°-40°	451.4	94.2
0°-60°	477.0	99.6
0°-90°	479.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	479.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	522	
5°	499	48
15°	505	138
25°	352	161
35°	168	104
45°	26	23
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1273493

CATALOG NUMBER: P3AS05R609830DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	521.6
2.5°	513.1
5°	499.0
7.5°	498.3
10°	507.9
12.5°	514.2
15°	504.6
17.5°	475.7
20°	433.5
22.5°	389.4
25°	352.3
27.5°	316.0
30°	273.0
32.5°	222.7
35°	168.2
37.5°	114.8
40°	72.2
42.5°	43.3
45°	25.6
47.5°	14.8
50°	7.8
52.5°	2.6
55°	1.9
57.5°	1.5
60°	1.5
62.5°	1.1
65°	1.1
67.5°	1.1
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)