

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273515

Luminaire Tested: P3AS05R609830DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273515
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609830DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 98CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 269.0 lumens
Efficiency: N/A
Efficacy: 37.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273515

CATALOG NUMBER: P3AS05R609830DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1273515

CATALOG NUMBER: P3AS05R609830DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72		
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66		
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62		
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57		
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54		
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50		
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68174
5°	66652
10°	62390
15°	55982
20°	48141
25°	39801
30°	31448
35°	23343
40°	16087
45°	10079
50°	5561
55°	3250
60°	2938
65°	2491
70°	2116
75°	2203
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 10079 cd/sqm

TEST NUMBER: P1273515

CATALOG NUMBER: P3AS05R609830DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.2	10.5
10°-20°	68.5	25.5
20°-30°	75.1	27.9
30°-40°	54.7	20.3
40°-50°	25.9	9.6
50°-60°	8.5	3.1
60°-70°	4.8	1.8
70°-80°	2.6	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	171.8	63.9
0°-40°	226.5	84.2
0°-60°	260.8	97.0
0°-90°	269.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	269.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	311	
5°	303	28
15°	247	68
25°	164	75
35°	87	55
45°	32	26
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1273515

CATALOG NUMBER: P3AS05R609830DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	310.9
2.5°	309.0
5°	302.8
7.5°	293.1
10°	280.2
12.5°	264.7
15°	246.6
17.5°	227.0
20°	206.3
22.5°	185.2
25°	164.5
27.5°	143.8
30°	124.2
32.5°	105.4
35°	87.2
37.5°	71.0
40°	56.2
42.5°	43.3
45°	32.5
47.5°	23.7
50°	16.3
52.5°	10.7
55°	8.5
57.5°	7.4
60°	6.7
62.5°	5.5
65°	4.8
67.5°	4.1
70°	3.3
72.5°	3.0
75°	2.6
77.5°	1.8
80°	1.5
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)