

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272534

Luminaire Tested: P3AS17R709827DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272534
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R709827DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 98CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 787.0 lumens
Efficiency: N/A
Efficacy: 38.6 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272534

CATALOG NUMBER: P3AS17R709827DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1272534

CATALOG NUMBER: P3AS17R709827DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	184590
5°	181201
10°	170872
15°	155075
20°	135648
25°	114418
30°	93685
35°	72678
40°	52012
45°	32934
50°	16443
55°	10055
60°	8640
65°	7939
70°	6988
75°	6524
80°	5556
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 32934 cd/sqm

TEST NUMBER: P1272534

CATALOG NUMBER: P3AS17R709827DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.8	9.8
10°-20°	190.1	24.2
20°-30°	216.5	27.5
30°-40°	169.3	21.5
40°-50°	83.1	10.6
50°-60°	25.6	3.2
60°-70°	15.1	1.9
70°-80°	8.1	1.0
80°-90°	2.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	483.4	61.4
0°-40°	652.6	82.9
0°-60°	761.4	96.7
0°-90°	787.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	787.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	842	
5°	823	77
15°	683	190
25°	473	216
35°	272	169
45°	106	83
55°	26	26
65°	15	15
75°	8	8
85°	2	2
90°	0	

TEST NUMBER: P1272534

CATALOG NUMBER: P3AS17R709827DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	841.8
2.5°	837.5
5°	823.2
7.5°	800.2
10°	767.4
12.5°	729.1
15°	683.1
17.5°	633.8
20°	581.3
22.5°	526.6
25°	472.9
27.5°	420.4
30°	370.0
32.5°	319.7
35°	271.5
37.5°	225.5
40°	181.7
42.5°	141.2
45°	106.2
47.5°	74.4
50°	48.2
52.5°	31.7
55°	26.3
57.5°	23.0
60°	19.7
62.5°	17.5
65°	15.3
67.5°	13.1
70°	10.9
72.5°	8.8
75°	7.7
77.5°	6.6
80°	4.4
82.5°	3.3
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)