

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1273521

Luminaire Tested: P3AS05R659830DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1273521
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659830DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 98CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 458.0 lumens
Efficiency: N/A
Efficacy: 63.6 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1273521
CATALOG NUMBER: P3AS05R659830DE010 E3CD1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1273521
 CATALOG NUMBER: P3AS05R659830DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93				93
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87				87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	87	85	83	81				81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75				75
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70				70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66				66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62				62
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58				58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54				54
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51				51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	111921
5°	105349
10°	104006
15°	102157
20°	96468
25°	89521
30°	69580
35°	40261
40°	16230
45°	7474
50°	2900
55°	1147
60°	965
65°	986
70°	962
75°	932
80°	884
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7474 cd/sqm



TEST NUMBER: P1273521
 CATALOG NUMBER: P3AS05R659830DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.5	9.9
10°-20°	125.7	27.4
20°-30°	164.5	35.9
30°-40°	95.3	20.8
40°-50°	20.4	4.5
50°-60°	3.3	0.7
60°-70°	1.8	0.4
70°-80°	1.1	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	335.7	73.3
0°-40°	431.0	94.1
0°-60°	454.7	99.3
0°-90°	458.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	458.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	510	
5°	479	45
15°	450	126
25°	370	165
35°	150	95
45°	24	20
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1273521
CATALOG NUMBER: P3AS05R659830DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	510.4
2.5°	496.0
5°	478.6
7.5°	471.5
10°	467.1
12.5°	460.8
15°	450.0
17.5°	433.4
20°	413.4
22.5°	394.5
25°	370.0
27.5°	328.9
30°	274.8
32.5°	213.0
35°	150.4
37.5°	95.2
40°	56.7
42.5°	35.6
45°	24.1
47.5°	15.6
50°	8.5
52.5°	4.1
55°	3.0
57.5°	2.6
60°	2.2
62.5°	2.2
65°	1.9
67.5°	1.5
70°	1.5
72.5°	1.1
75°	1.1
77.5°	0.7
80°	0.7
82.5°	0.4
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)