

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1272578

Luminaire Tested: P3AS20R209827D010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1272578
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R209827D010 E3D1WH
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 98CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1783.0 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1272578

CATALOG NUMBER: P3AS20R209827D010 E3D1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1272578

CATALOG NUMBER: P3AS20R209827D010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	114	112	110		113	111	110	108		107	106	105		104	103	102		100	100	99
2	112	109	106	104		110	107	105	103		104	102	101		101	100	98		99	98	96
3	109	105	102	99		107	104	101	98		101	99	97		99	97	95		97	95	94
4	106	101	98	95		105	100	97	95		99	96	94		97	95	93		95	93	92
5	104	98	95	92		102	98	94	92		96	93	91		95	92	90		93	91	90
6	101	96	92	89		100	95	92	89		94	91	89		93	90	88		92	89	88
7	99	93	90	87		98	93	89	87		92	89	86		91	88	86		90	87	86
8	97	91	87	85		96	91	87	85		90	87	85		89	86	84		88	86	84
9	95	89	85	83		94	89	85	83		88	85	83		87	84	83		87	84	82
10	93	87	84	81		92	87	83	81		86	83	81		86	83	81		85	83	81

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2704674
5°	2277212
10°	1422329
15°	531740
20°	182529
25°	76069
30°	35828
35°	16062
40°	7586
45°	3876
50°	1433
55°	268
60°	307
65°	363
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3876 cd/sqm

TEST NUMBER: P1272578

CATALOG NUMBER: P3AS20R209827D010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	860.3	48.3
10°-20°	708.6	39.7
20°-30°	161.0	9.0
30°-40°	41.0	2.3
40°-50°	10.3	0.6
50°-60°	1.3	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1730.0	97.0
0°-40°	1771.0	99.3
0°-60°	1782.6	100.0
0°-90°	1783.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1783.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12334	
5°	10345	860
15°	2342	709
25°	314	161
35°	60	41
45°	12	10
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1272578

CATALOG NUMBER: P3AS20R209827D010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	12334.3
1°	12229.7
2°	11921.6
3°	11479.6
4°	10937.2
5°	10345.4
6°	9685.9
7°	8958.1
8°	8109.0
9°	7267.5
10°	6387.8
11°	5451.5
12°	4516.7
13°	3724.7
14°	2967.7
15°	2342.3
16°	1848.8
17°	1458.4
18°	1171.9
19°	953.0
20°	782.2
21°	653.9
22°	545.9
23°	453.8
24°	378.5
25°	314.4
27.5°	205.7
30°	141.5
32.5°	87.1
35°	60.0
37.5°	38.3
40°	26.5
42.5°	18.1
45°	12.5
47.5°	8.4
50°	4.2
52.5°	2.1
55°	0.7
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0

TEST NUMBER: P1272578

CATALOG NUMBER: P3AS20R209827D010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)